



产品认证证书

证书编号: CQC17003177724

申请人名称及地址

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

制造商名称及地址

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

生产企业名称及地址

Wieland Electric s.r.o. (V026734)
Nadrazni 1557, 35601 Sokolov Czech Republic

产品名称和系列、规格、型号

电连接器

See Appendix

产品标准和技术要求

GB/T34989-2017

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462222-2011 认证规则的要求, 特发此证。

发证日期: 2019 年 04 月 23 日

本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2017 年 09 月 29 日

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0144777



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC17003177724

NAME AND ADDRESS OF THE APPLICANT

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

NAME AND ADDRESS OF THE FACTORY

Wieland Electric s.r.o. (V026734)
Nadrazni 1557, 35601 Sokolov Czech Republic

PRODUCT NAME, MODEL AND SPECIFICATION

Electrical Connector
See Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T34989-2017

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462222-2011 .

Valid from: Apr.23,2019

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

Date of original issued: Sep.29,2017

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0144777



产品认证证书

附 录

第 1 页 共 2 页

证书编号: CQC17003177724

纸 号: 144777

系列命名规则:

RST 16i 系列

16A 50V/250V/400V 额定脉冲电压 4kV 无分断能力 2、3、4、5 极 IP66/68 不带联锁 无负载 100 次操作循环 40T100 污染等级 3 过电压保护类别 III 灼热丝 850℃ 针焰 30s 球压 125℃ PTI400

系列命名如下:

RST 16i 3 S B1 M02 L BR

(1) (2) (3) (4) (5) (6) (7)

1	系列	RST16i	RST16i
2	芯数	3/2	2 芯
		3	3 芯
		5/4	4 芯
		5	5 芯
3	连接方式	S	螺纹夹紧
4	插针类型	B	母头, 1 表示接入电缆数为 1
		S	公头, 1 表示接入电缆数为 1
5	出线方向及安装孔径	ZT4(S)	线端水平出线, 外径 5-9.5mm
		ZT6(S)	线端水平出线, 外径 7.1-13mm
		M02	板端出线, 公制 M16 开孔
		M03	板端出线, 公制 M20.2 开孔

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 2 页 共 2 页

证书编号: CQC17003177724

纸 号: 144777

6	额定电压	无	250V (2、3 芯); 250V/400V (4、5 芯)
		H	400V
		L	50V
		A	250V/400V
7	插芯颜色	GL	浅灰色
		SW	黑色
		BR	棕色
		GN	绿色
		BL	淡蓝色
		TB	青绿色

注: 此附录与证书同时使用时有效。

主任: 陆杨



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>