

Certificate of Compliance

Certificate: 1083359

Master Contract: 165750

Project: 2481052

Date Issued: March 22, 2012

Issued to: Wieland Electric GmbH
Brennerstrasse 10-14
96045 Bamberg
GERMANY

The products listed below are eligible to bear the CSA Mark shown



Issued by: G. Foulem
G. Foulem

PRODUCTS

CLASS 6233 01 – RECEPTACLES – Attachment Plug Type and Plugs

S-Use Connectors, Types 8113, 8213, 8313, 8413, rated 300 V, 15 A, 22-12 AWG solid and stranded copper conductors for all variations, except for tab connections; Suffix SE rated 10 A; Suffix DFWW rated 6.5 A; Suffix DFLS rated 8 A; Suffix BSK rated 300V, 3 A, 20-18 AWG; Suffix BK rated 13 A for 14 AWG, 11 A for 16 AWG, 10 A for 18 AWG, 6 A for 20 AWG; Suffixes BFK, SUFK, rated 300V, 12A; Type 8113/8213 BL..TR, B /3/2 through /23/12 and S /3/2 through /23/12, rated 600V, 12 A, 18-12 AWG; Suffix SU, rated 12 A, 300V; Type 8113, with Suffixes S /4 OL, S /4 OR, 300 V, 10 A; Suffix F2, latching mechanism.

S-Use Connectors, Series 8813 rated 300 V, 5 A, 22-14 AWG.

Notes:

1. Certified as a component for use only where the suitability of the final combination is determined by CSA International or other NRTL.
2. The connectors may be acceptable at voltages greater than rated voltage when they are components of Certified electrical equipment permitting small spacings.
3. The connectors are not for interrupting current.
4. Suffixes may be added to the Catalogue numbers to denote mechanical variations not affecting the electrical properties.