

product data sheet

item no. 02.126.6200.8

female contact 0,75/18

revos POWER, female contact 0,75/18



item no.	02.126.6200.8
EAN	4049088213250
order unit	100 piece(s)

certificates / approvals

technical data

general

min. conductor cross section flexible wire	0.75 mm ²
min. UL/CSA wire diameter flexible wire	18 AWG
max. UL/CSA wire diameter flexible wire	18 AWG
connection type	crimp
material	copper
contact pin diameter	2.5 mm

accessories

item no.	type	description
05.502.5000.0	crimping die H	
05.502.5200.0	contact positioner 6	
95.101.0800.0	basic crimping tool .	Crimping tool kit
05.502.0710.0	extraction tool MOD. 10POL.	Extraction tool for 10 pole revos FLEX module

