

product data sheet

item no. 02.126.5800.8

female contact 1,5/16

revos POWER, female contact 0,5/20

item no.	02.126.5800.8
EAN	4049088213212
order unit	100 piece(s)

certificates / approvals

technical data

general

min. conductor cross section flexible wire	1.5 mm²
max. conductor cross section flexible wire	1.5 mm²
min. UL/CSA wire diameter flexible wire	16 AWG
max. UL/CSA wire diameter flexible wire	16 AWG
connection type	crimp
material	copper
contact pin diameter	1.6 mm

accessories

item no.	type	description
05.502.4900.0	crimping die G	
05.502.5100.0	contact positioner 5	
95.101.0800.0	basic crimping tool .	Crimping tool kit
05.502.0710.0	extraction tool MOD. 10POL.	Extraction tool for 10 pole revos FLEX module
05.502.4400.0	extraction tool 4,0MM	Extraction tool for turned contacts with a diameter of 4 mm

