

## product data sheet

item no. 70.800.3256.0

### female insert BAS BUCK 32 50 PC

Female insert revos basic, 32-poles, polycarbonate insert, rated current: 16A, rated voltage: 500V, with gold-plated or silver-plated contacts



|            |               |
|------------|---------------|
| item no.   | 70.800.3256.0 |
| EAN        | 4015573861923 |
| order unit | 5 piece(s)    |

### certificates / approvals



### technical data

#### general

|                                                            |               |
|------------------------------------------------------------|---------------|
| model                                                      | female insert |
| inflammability class of insulation material acc. with UL94 | V0            |
| color                                                      | grey          |
| pollution degree                                           | 3             |
| suitable for modular version                               | no            |
| alternative size                                           | 16H           |
| operating temperature range min.                           | -40 °C        |
| operating temperature range max.                           | 120 °C        |

#### connection data

|                                                |       |
|------------------------------------------------|-------|
| connection type                                | crimp |
| number of poles                                | 32    |
| plus switching contacts                        | 0     |
| number of pole for rated current 2             | 0     |
| number of pole for rated current 3             | 0     |
| total number of poles (without ground contact) | 32    |
| with wire protection                           | no    |
| protective contact                             | yes   |

#### technical data UL/CSA

|                                            |           |
|--------------------------------------------|-----------|
| nominal voltage according to UL/CSA        | 600 V     |
| nominal current according CSA              | 16 A      |
| min. conductor cross section flexible wire | 0.5 mm²   |
| max. conductor cross section flexible wire | 2.5 mm²   |
| conductor cross section flexible AWG wire  | 20-12 AWG |

#### model

|              |    |
|--------------|----|
| with housing | no |
|--------------|----|

#### contacts

|                  |              |
|------------------|--------------|
| contact material | copper alloy |
|------------------|--------------|

|                    |                           |
|--------------------|---------------------------|
| surface            | silver and/or gold plated |
| contact resistance | # 1.5 mOhm                |
| wire strip length  | 7 mm                      |

**screws head design/recomm. Torque**

|                         |               |
|-------------------------|---------------|
| mounting screws         | H1/0.5-0.7 Nm |
| ground conductor screws | H2/1.2-1.6 Nm |

**technical data DIN EN 61984**

|                             |       |
|-----------------------------|-------|
| nominal voltage             | 500 V |
| nominal voltage face/ground | 500 V |
| nominal current             | 16 A  |
| rated impulse voltage       | 6 kV  |

**assembly**

| item no.      | type                         | description                                                                                                                                            |
|---------------|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| 71.350.1635.0 | hood BAS GOT GG 16 M25 A0    | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the right side (IP54), low version, 16-poles                       |
| 71.350.1635.1 | hood BAS GOT GG 16 M25 A1    | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the right side, low version, 16-poles                            |
| 71.350.1635.2 | hood BAS GOT GG 16 M25 A2    | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the right side, low version, 16-poles                                    |
| 71.350.1635.3 | hood BAS GOT GG 16 M25 A3    | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the right side (IP54), low version, 16-poles                     |
| 71.352.1635.0 | hood BAS GOT GI 16 M25 A0    | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the top (IP54), low version, 16-poles                              |
| 71.352.1635.1 | hood BAS GOT GI 16 M25 A1    | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the top, low version, 16-poles                                   |
| 71.352.1635.2 | hood BAS GOT GI 16 M25 A2    | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the top, low version, 16-poles                                           |
| 71.352.1635.3 | hood BAS GOT GI 16 M25 A3    | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the top (IP54), low version, 16-poles                            |
| 71.353.1635.0 | hood BAS GOT GG 16 M32 A0    | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the right side (IP54), low version, 16-poles                       |
| 71.353.1635.1 | hood BAS GOT GG 16 M32 A1    | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the right side, low version, 16-poles                            |
| 71.353.1635.2 | hood BAS GOT GG 16 M32 A2    | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the right side, low version, 16-poles                                    |
| 71.353.1635.3 | hood BAS GOT GG 16 M32 A3    | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the right side (IP54), low version, 16-poles                     |
| 71.354.1635.0 | hood BAS GOT GI 16 M32 A0    | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the top (IP54), low version, 16-poles                              |
| 71.354.1635.1 | hood BAS GOT GI 16 M32 A1    | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the top, low version, 16-poles                                   |
| 71.354.1635.2 | hood BAS GOT GI 16 M32 A2    | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the top, low version, 16-poles                                           |
| 71.354.1635.3 | hood BAS GOT GI 16 M32 A3    | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the top (IP54), low version, 16-poles                            |
| 71.372.1635.0 | hood BAS GOT GL 16 M25 A0    | Hood revos basic made of aluminum, with single locking lever and cable gland M25 on the top - free cable connection (IP54), low version, 16-poles      |
| 71.372.1635.1 | hood BAS GOT GL 16 M25 A1    | Hood revos basic made of aluminum, with single locking lever and threaded hole M25 on the top - free cable connection, low version, 16-poles           |
| 71.372.1635.3 | hood BAS GOT GL 16 M25 A3    | Hood revos basic made of aluminum, with single locking lever and trumpet gland M25 on the top - free cable connection (IP54), low version, 16-poles    |
| 71.450.1637.1 | hood BAS GOM GG16 M25 B1     | Hood revos basic metal-series without coating, for single locking lever with threaded hole M25 on the right side, low version, 16-poles                |
| 71.452.1637.1 | hood BAS GOM GI16 M25 B1     | Hood revos basic metal-series without coating, for single locking lever with threaded hole M25 on the top, low version, 16-poles                       |
| 71.472.1637.1 | hood BAS GOM GL16 M25 B1     | Hood revos basic metal-series without coating, with single locking lever and threaded hole B1 on the top - free cable connection, low version,M2-poles |
| 76.350.4035.0 | hood BAS GOT GG 40HM25 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the right side (IP54), low version, 40-poles                       |
| 76.350.4035.1 | hood BAS GOT GG 40HM25 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the right side, low version, 40-poles                            |
| 76.350.4035.2 | hood BAS GOT GG 40HM25 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the right side, low version, 40-poles                                    |

|               |                              |                                                                                                                                                                             |
|---------------|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 76.350.4035.3 | hood BAS GOT GG 16H M25 A3   | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the right side (IP54), low version, 16-poles                                          |
| 76.351.1635.0 | hood BAS GOT GH 10H M20 A0   | Hood revos basic made of aluminum, for single locking lever with cable gland M20 on the front (IP54), low version, 10-poles                                                 |
| 76.351.1635.1 | hood BAS GOT GH 16H M20 A1   | Hood revos basic made of aluminum, for single locking lever with threaded hole M20 on the front, low version, 16-poles                                                      |
| 76.351.1635.2 | hood BAS GOT GH 10H M20 A2   | Hood revos basic made of aluminum, for single locking lever with nozzleM20 on the front, low version, 10-poles                                                              |
| 76.351.1635.3 | hood BAS GOT GH 10H M20 A3   | Hood revos basic made of aluminum, for single locking lever with trumpet gland M20 on the front (IP54), low version, 10-poles                                               |
| 76.352.4035.0 | hood BAS GOT GI 40HM25 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the top (IP54), low version, 40-poles                                                   |
| 76.352.4035.1 | hood BAS GOT GI 16HM25 A1    | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the top, low version, 16-poles                                                        |
| 76.352.4035.2 | hood BAS GOT GI 40HM25 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the top, low version, 40-poles                                                                |
| 76.352.4035.3 | hood BAS GOT GI 16H M25 A3   | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the top (IP54), low version, 16-poles                                                 |
| 76.353.4035.0 | hood BAS GOT GG 40HM32 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the right side (IP54), high version, size 16H                                           |
| 76.353.4035.1 | hood BAS GOT GG 16HM32 A1    | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the right side, low version, 16-poles                                                 |
| 76.353.4035.2 | hood BAS GOT GG 40HM32 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the right side, low version, 40-poles                                                         |
| 76.353.4035.3 | hood BAS GOT GG 16H M32 A3   | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the right side (IP54), low version, 16-poles                                          |
| 76.354.4035.0 | hood BAS GOT GI 40HM32 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the top (IP54), low version, 40-poles                                                   |
| 76.354.4035.1 | hood BAS GOT GI 40HM32 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the top, low version, 40-poles                                                        |
| 76.354.4035.2 | hood BAS GOT GI 40HM32 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the top, low version, 40-poles                                                                |
| 76.354.4035.3 | hood BAS GOT GI 16H M32 A3   | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the top (IP54), low version, 16-poles                                                 |
| 76.360.4035.0 | hood BAS GOT GG 16H M40 A0   | Hood revos basic made of aluminum, for single locking lever with cable gland M40 on the right side (IP54), low version, 16-poles                                            |
| 76.360.4035.1 | hood BAS GOT GG 40HM40 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M40 on the right side, low version, 40-poles                                                 |
| 76.362.4035.1 | hood BAS GOT GI 40HM40 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M40 on the top, low version, 40-poles                                                        |
| 76.374.4035.0 | hood BAS GOT GL 40HM32 50 A0 | Connectors for free cable connections revos basic made of aluminum, with single locking lever and cable gland M32 on the top - free cable connection (IP54), 40-poles       |
| 71.320.1628.0 | bottom BAS GUT GK 16 A       | Bottom-base revos basic made of aluminum, with single locking lever, open, low version, 16-poles                                                                            |
| 71.325.1628.0 | bottom BAS GUT GP 16 A       | Bottom-base revos basic made of aluminum, with single locking lever, open, low version, 16-poles                                                                            |
| 71.330.1635.0 | bottom BAS GUT GL 16 M25 A0  | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the right and left side (IP54), low version, 16-polig                            |
| 71.330.1635.1 | bottom BAS GUT GL 16 M25 A1  | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right and left side, low version, 16-polig                                 |
| 71.331.1635.0 | bottom BAS GUT GM 16 M25 A0  | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the left side (IP54), low version, 16-polig                                      |
| 71.331.1635.1 | bottom BAS GUT GM 16 M25 A1  | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the left side, low version, 16-polig                                           |
| 71.333.1635.0 | bottom BAS GUT GO 16 M25 A0  | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the bottom (IP54), low version, 16-polig                                         |
| 71.333.1635.1 | bottom BAS GUT GO 16 M25 A1  | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the bottom, low version, 16-polig                                              |
| 71.340.1635.0 | bottom BAS GUT GR 16 M25 A0  | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the right and the left side, with protective cover (IP54), low version, 16-polig |
| 71.340.1635.1 | bottom BAS GUT GR 16 M25 A1  | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right and the left side, with protective cover, low version, 16-polig      |
| 71.341.1635.0 | bottom BAS GUT GS 16 M25 A0  | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the left side, with protective cover (IP54), low version, 16-polig               |
| 71.341.1635.1 | bottom BAS GUT GS 16 M25 A1  | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the left side, with protective cover, low version, 16-polig                    |
| 71.342.1635.0 | bottom BAS GUT GT 16 M25 A0  | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the right side, with protective cover (IP54), low version, 16-polig              |

|               |                                |                                                                                                                                                                                    |
|---------------|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 71.342.1635.1 | bottom BAS GUT GT 16 M25 A1    | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right side, with protective cover, low version, 16-polig                          |
| 71.343.1635.0 | bottom BAS GUT GU 16 M25 A0    | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the bottom, with protective cover (IP54), low version, 16-polig                         |
| 71.343.1635.1 | bottom BAS GUT GU 16 M25 A1    | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the bottom, with protective cover, low version, 16-polig                              |
| 71.420.1637.0 | bottom BAS GUM GK 16 B         | Bottom-base revos basic metal-series without coating, open, low version, 16-poles                                                                                                  |
| 71.425.1637.0 | bottom BAS GUM GP 16 B         | Bottom-base revos basic metal-series without coating, with single locking lever and protective cover, low version, 16-poles                                                        |
| 71.430.1637.1 | bottom BAS GUM GL 16 M25 B1    | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the right and left side, low version, 16-polig                            |
| 71.431.1637.1 | bottom BAS GUM GM 16 M25 B1    | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the left side, low version, 16-polig                                      |
| 71.440.1637.1 | bottom BAS GUM GR 16 M25 B1    | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the right and the left side, with protective cover, low version, 16-polig |
| 71.441.1637.1 | bottom BAS GUM GS 16 M25 B1    | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the left side, with protective cover, low version, 16-polig               |
| 76.330.4035.0 | bottom BAS GUT GL 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the right and left side (IP54), low version, 40-polig                                   |
| 76.330.4035.1 | bottom BAS GUT GL 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right and left side, low version, 40-polig                                        |
| 76.331.4035.0 | bottom BAS GUT GM 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the left side (IP54), low version, 40-polig                                             |
| 76.331.4035.1 | bottom BAS GUT GM 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the left side, low version, 40-polig                                                  |
| 76.333.4035.0 | bottom BAS GUT GO 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the bottom (IP54), low version, 40-polig                                                |
| 76.333.4035.1 | bottom BAS GUT GO 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the bottom, low version, 40-polig                                                     |
| 76.334.4035.0 | bottom BAS GUT GL 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the right and left side (IP54), low version, 40-polig                                   |
| 76.334.4035.1 | bottom BAS GUT GL 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the right and left side, low version, 40-polig                                        |
| 76.335.4035.0 | bottom BAS GUT GM 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the left side (IP54), low version, 40-polig                                             |
| 76.335.4035.1 | bottom BAS GUT GM 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the left side, low version, 40-polig                                                  |
| 76.337.4035.0 | bottom BAS GUT GO 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the bottom (IP54), low version, 40-polig                                                |
| 76.337.4035.1 | bottom BAS GUT GO 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the bottom, low version, 40-polig                                                     |
| 76.340.4035.0 | bottom BAS GUT GR 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the right and the left side, with protective cover (IP54), low version, 40-polig        |
| 76.340.4035.1 | bottom BAS GUT GR 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right and the left side, with protective cover, low version, 40-polig             |
| 76.341.4035.0 | bottom BAS GUT GS 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the left side, with protective cover (IP54), low version, 40-polig                      |
| 76.341.4035.1 | bottom BAS GUT GS 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the left side, with protective cover, low version, 40-polig                           |
| 76.342.4035.0 | bottom BAS GUT GT 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the right side, with protective cover (IP54), low version, 40-polig                     |
| 76.342.4035.1 | bottom BAS GUT GT 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right side, with protective cover, low version, 40-polig                          |
| 76.343.4035.0 | bottom BAS GUT GU 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M25 on the bottom, with protective cover (IP54), low version, 40-polig                         |
| 76.343.4035.1 | bottom BAS GUT GU 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the bottom, with protective cover, low version, 40-polig                              |
| 76.344.4035.0 | bottom BAS GUT GR 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the right and the left side, with protective cover (IP54), low version, 40-polig        |
| 76.344.4035.1 | bottom BAS GUT GR 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the right and the left side, with protective cover, low version, 40-polig             |
| 76.345.4035.0 | bottom BAS GUT GS 16HM32 A0    | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the left side, with protective cover (IP54), low version, 16-polig                      |
| 76.345.4035.1 | bottom BAS GUT GS 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the left side, with protective cover, low version, 40-polig                           |
| 76.346.4035.0 | bottom BAS GUT GT 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the right side, with protective cover (IP54), low version, 40-polig                     |
| 76.346.4035.1 | bottom BAS GUT GT 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the right side, with protective cover, low version, 40-polig                          |

|               |                                |                                                                                                                                                            |
|---------------|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 76.347.4035.0 | bottom BAS GUT GU 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the bottom, with protective cover (IP54), low version, 40-polig |
| 76.347.4035.1 | bottom BAS GUT GU 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M32 on the bottom, with protective cover, low version, 40-polig      |
| 70.350.1635.0 | hood BAS GOT GA 16 M25 A0      | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the right side (IP54), low version, 16-poles             |
| 70.350.1635.1 | hood BAS GOT GA 16 M25 A1      | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the right side, low version, 16-poles                  |
| 70.350.1635.2 | hood BAS GOT GA 16 M25 A2      | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the right side, low version, 16-poles                         |
| 70.350.1635.3 | hood BAS GOT GA 16 M25 A3      | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the right side (IP54), low version, 16-poles           |
| 70.352.1635.0 | hood BAS GOT GC 16 M25 A0      | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the top (IP54), low version, 16-poles                    |
| 70.352.1635.1 | hood BAS GOT GC 16 M25 A1      | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the top, low version, 16-poles                         |
| 70.352.1635.2 | hood BAS GOT GC 16 M25 A2      | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the top, low version, 16-poles                                |
| 70.352.1635.3 | hood BAS GOT GC 16 M25 A3      | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the top (IP54), low version, 16-poles                  |
| 70.353.1635.0 | hood BAS GOT GA 16 M32 A0      | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the right side (IP54), low version, 16-poles             |
| 70.353.1635.1 | hood BAS GOT GA 16 M32 A1      | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the right side, low version, 16-poles                  |
| 70.353.1635.2 | hood BAS GOT GA 16 M32 A2      | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the right side, low version, 16-poles                         |
| 70.353.1635.3 | hood BAS GOT GA 16 M32 A3      | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M32 on the right side (IP54), low version, 16-poles           |
| 70.354.1635.0 | hood BAS GOT GC 16 M32 A0      | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the top (IP54), low version, 16-poles                    |
| 70.354.1635.1 | hood BAS GOT GC 16 M32 A1      | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the top, low version, 16-poles                         |
| 70.354.1635.2 | hood BAS GOT GC 16 M32 A2      | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the top, low version, 16-poles                                |
| 70.354.1635.3 | hood BAS GOT GC 16 M32 A3      | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M32 on the top (IP54), low version, 16-poles                  |
| 70.355.1635.0 | hood BAS GOT GD 16 M25 A0      | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the right side (IP54), low version, 16-poles                           |
| 70.355.1635.1 | hood BAS GOT GD 16 M25 A1      | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the right side, low version, 16-poles                                |
| 70.355.1635.2 | hood BAS GOT GD 16 M25 A2      | Hood revos basic made of aluminum, with double locking lever and nozzle M25 on the right side, low version, 16-poles                                       |
| 70.355.1635.3 | hood BAS GOT GD 16 M25 A3      | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the right side (IP54), low version, 16-poles                         |
| 70.357.1635.0 | hood BAS GOT GF 16 M25 A0      | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the top (IP54), low version, 16-poles                                  |
| 70.357.1635.1 | hood BAS GOT GF 16 M25 A1      | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the top, low version, 16-poles                                       |
| 70.357.1635.2 | hood BAS GOT GF 16 M25 A2      | Hood revos basic made of aluminum, with double locking lever and nozzle M25 on the top, low version, 16-poles                                              |
| 70.357.1635.3 | hood BAS GOT GF 16 M25 A3      | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the top (IP54), low version, 16-poles                                |
| 70.358.1635.0 | hood BAS GOT GD 16 M32 A0      | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the right side (IP54), low version, 16-poles                           |
| 70.358.1635.1 | hood BAS GOT GD 16 M32 A1      | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the right side, low version, 16-poles                                |
| 70.358.1635.2 | hood BAS GOT GD 16 M32 A2      | Hood revos basic made of aluminum, with double locking lever and nozzle M32 on the right side, low version, 16-poles                                       |
| 70.358.1635.3 | hood BAS GOT GD 16 M32 A3      | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the right side (IP54), low version, 16-poles                         |
| 70.359.1635.0 | hood BAS GOT GF 16 M32 A0      | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the top (IP54), low version, 16-poles                                  |
| 70.359.1635.1 | hood BAS GOT GF 16 M32 A1      | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the top, low version, 16-poles                                       |
| 70.359.1635.2 | hood BAS GOT GF 16 M32 A2      | Hood revos basic made of aluminum, with double locking lever and nozzle M32 on the top, low version, 16-poles                                              |
| 70.359.1635.3 | hood BAS GOT GF 16 M32 A3      | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the top (IP54), low version, 16-poles                                |

|               |                              |                                                                                                                                                     |
|---------------|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| 70.372.1635.0 | hood BAS GOT GK 16 M25 A0    | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the top - free cable connection (IP54), low version, 16-poles   |
| 70.372.1635.1 | hood BAS GOT GK 16 M25 A1    | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the top - free cable connection, low version, 16-poles        |
| 70.372.1635.3 | hood BAS GOT GK 16 M25 A3    | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the top - free cable connection (IP54), low version, 16-poles |
| 72.250.1635.2 | hood POW GOT GA 16 M40 69 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M40 on the right side, low version, 16-poles                  |
| 73.350.4035.0 | hood BAS GOT GA 16HM25 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the right side (IP54), low version, 16-poles      |
| 73.350.4035.1 | hood BAS GOT GA 16HM25 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the right side, high version, 16-poles          |
| 73.350.4035.2 | hood BAS GOT GA 16HM25 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the right side, low version, 16-poles                  |
| 73.350.4035.3 | hood BAS GOT GA 16H M25 A3   | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the right side (IP54), low version, 16-poles    |
| 73.351.1635.0 | hood BAS GOT GB 16H M25 A0   | Hood revos basic made of aluminum, for double locking lever and cable gland M25 on the front (IP54), low version, 16-poles                          |
| 73.351.1635.1 | hood BAS GOT GB 16H M25 A1   | Hood revos basic made of aluminum, for double locking lever and threaded hole M25 on the front, low version, 16-poles                               |
| 73.351.1635.2 | hood BAS GOT GB 16H M25 A2   | Hood revos basic made of aluminum, for double locking lever and nozzle M25 on the front, low version, 16-poles                                      |
| 73.351.1635.3 | hood BAS GOT GB 16H M25 A3   | Hood revos basic made of aluminum, for double locking lever and trumpet gland M25 on the front (IP54), low version, 16-poles                        |
| 73.352.4035.0 | hood BAS GOT GC 16HM25 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the top (IP54), low version, 16-poles             |
| 73.352.4035.1 | hood BAS GOT GC 16HM25 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the top, low version, 16-poles                  |
| 73.352.4035.2 | hood BAS GOT GC 16HM25 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the top, low version, 16-poles                         |
| 73.352.4035.3 | hood BAS GOT GC 16H M25 A3   | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the top (IP54), low version, 16-poles           |
| 73.353.4035.0 | hood BAS GOT GA 40HM32 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the right side (IP54), high version, 40- poles    |
| 73.353.4035.1 | hood BAS GOT GA 40HM32 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the right side, high version, 40-poles          |
| 73.353.4035.2 | hood BAS GOT GA 40HM32 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the right side, low version, 40-poles                  |
| 73.353.4035.3 | hood BAS GOT GA 16HM32 A3    | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M32 on the right side (IP54), low version, 16-poles    |
| 73.354.4035.0 | hood BAS GOT GC 16HM32 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the top (IP54), low version, 16-poles             |
| 73.354.4035.1 | hood BAS GOT GC 16HM32 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the top, low version, 16-poles                  |
| 73.354.4035.2 | hood BAS GOT GC 16HM32 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the top, low version, 16-poles                         |
| 73.354.4035.3 | hood BAS GOT GC 16HM32 A2    | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the top, low version, 16-poles                         |
| 73.355.4035.0 | hood BAS GOT GD 16HM25 50 A0 | revos BASIC 500V size 16H hood with cable gland M25, lateral cable entry, with double locking levers, high design                                   |
| 73.355.4035.1 | hood BAS GOT GD 16HM25 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the right side, low version, 16-poles                         |
| 73.355.4035.2 | hood BAS GOT GD 16HM25 50 A2 | revos BASIC 500V size 16H hood with intermediate support M25, lateral cable entry, with double locking levers, high design                          |
| 73.355.4035.3 | hood BAS GOT GD 16HM25 A2    | Hood revos basic made of aluminum, with double locking lever and nozzle M25 on the right side, low version, 16-poles                                |
| 73.357.4035.0 | hood BAS GOT GF 16HM25 50 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the top (IP54), low version, 16-poles                           |
| 73.357.4035.1 | hood BAS GOT GF 16HM25 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the top, low version, 16-poles                                |
| 73.357.4035.2 | hood BAS GOT GF 16HM25 50 A2 | Hood revos basic made of aluminum, with double locking lever and nozzle M25 on the top, low version, 16-poles                                       |
| 73.357.4035.3 | hood BAS GOT GF 16HM25 A3    | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the top (IP54), low version, 16-poles                         |
| 73.358.4035.0 | hood BAS GOT GD 16HM32 50 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the right side (IP54), low version, 16-poles                    |
| 73.358.4035.1 | hood BAS GOT GD 16HM32 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the right side, low version, 16-poles                         |

|               |                                |                                                                                                                                                                        |
|---------------|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 73.358.4035.2 | hood BAS GOT GD 16HM32 50 A2   | Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the right side, low version, 16-poles                                                    |
| 73.358.4035.3 | hood BAS GOT GD 16HM32 A3      | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the right side (IP54), low version, 16-poles                                     |
| 73.359.4035.0 | hood BAS GOT GF 16HM32 50 A0   | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the top (IP54), low version, 16-poles                                              |
| 73.359.4035.1 | hood BAS GOT GF 16HM32 50 A1   | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the top, high version, 16-poles                                                  |
| 73.359.4035.2 | hood BAS GOT GF 16HM32 50 A2   | Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the top, low version, 16-poles                                                           |
| 73.359.4035.3 | hood BAS GOT GF 16HM32 A3      | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the top (IP54), low version, 16-poles                                            |
| 73.360.4035.0 | hood BAS GOT GA 16HM40 A0      | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M40 on the right side (IP54), low version, 16-poles                         |
| 73.360.4035.1 | hood BAS GOT GA 16HM40 50 A1   | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M40 on the right side, high version, 16-poles                             |
| 73.360.4035.2 | hood BAS GOT GA 16HM40 A2      | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M40 on the right side, low version, 16-poles                                     |
| 73.362.4035.0 | hood BAS GOT GC 16HM40 A0      | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M40 on the top (IP54), low version, 16-poles                                |
| 73.362.4035.1 | hood BAS GOT GC 16HM40 50 A1   | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M40 on the top, low version, 16-poles                                     |
| 70.320.1628.0 | bottom BAS GUT GA 16 A         | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap, low version, 16-poles                                                                |
| 70.325.1628.0 | bottom BAS GUT GE 16 A         | Bottom-base revos basic made of aluminum, for double locking lever and protective cover, open, low version, 16-poles                                                   |
| 70.330.1635.0 | bottom BAS GUT GB 16 M25 A0    | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right and left side (IP54), low version, 16-polig         |
| 70.330.1635.1 | bottom BAS GUT GB 16 M25 A1    | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right and left side, low version, 16-polig              |
| 70.331.1635.0 | bottom BAS GUT GC 16 M25 A0    | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the left side (IP54), low version, 16-polig                   |
| 70.331.1635.1 | bottom BAS GUT GC 16 M25 A1    | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the left side, low version, 16-polig                        |
| 70.333.1635.0 | bottom BAS GUT GD 16 M25 A0    | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right side (IP54), low version, 16-polig                  |
| 70.333.1635.1 | bottom BAS GUT GD 16 M25 A1    | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right side, low version, 16-polig                       |
| 70.340.1635.0 | bottom BAS GUT GF 16 M25 A0    | Bottom-base revos basic made of aluminum, for double locking lever withcable gland M25 on the left and right side, with protective cover (IP54), low version, 16-polig |
| 70.340.1635.1 | bottom BAS GUT GF 16 M25 A1    | Bottom-base revos basic made of aluminum, for double locking lever withthreaded hole M25 on the left and right side, with protective cover, low version, 16-polig      |
| 70.341.1635.0 | bottom BAS GUT GG 16 M25 A0    | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the left side, with protective cover (IP54), low version, 16-polig           |
| 70.341.1635.1 | bottom BAS GUT GG 16 M25 A1    | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the left side, with protective cover, low version,16-polig                 |
| 70.342.1635.0 | bottom BAS GUT GH 16 M25 A0    | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the right side, with protective cover (IP54), low version, 16-polig          |
| 70.342.1635.1 | bottom BAS GUT GH 16 M25 A1    | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the right side, with protective cover, low version, 16-polig               |
| 70.343.1635.0 | bottom BAS GUT GI 16 M25 A0    | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the bottom, with protective cover (IP54), low version, 16-polig              |
| 70.343.1635.1 | bottom BAS GUT GI 16 M25 A1    | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the bottom, with protective cover, low version, 16-polig                   |
| 73.330.4035.0 | bottom BAS GUT GB 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right and left side (IP54), low version, 16-polig         |
| 73.330.4035.1 | bottom BAS GUT GB 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right and left side, low version, 16-polig              |
| 73.331.4035.0 | bottom BAS GUT GC 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the left side (IP54), low version, 16-polig                   |
| 73.331.4035.1 | bottom BAS GUT GC 16M25 50 A1  | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the left side, low version, 16-polig                        |
| 73.333.4035.0 | bottom BAS GUT GD 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right side (IP54), low version, 16-polig                  |
| 73.333.4035.1 | bottom BAS GUT GD 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right side, low version, 16-polig                       |
| 73.334.4035.0 | bottom BAS GUT GB 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M32 on the right and left side (IP54), low version, 16-polig         |

|               |                                |                                                                                                                                                                         |
|---------------|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 73.334.4035.1 | bottom BAS GUT GB 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the right and left side, low version, 16-polig               |
| 73.335.4035.0 | bottom BAS GUT GC 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M32 on the left side (IP54), high version, 6-poles                    |
| 73.335.4035.1 | bottom BAS GUT GC 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the left side, low version, 16-polig                         |
| 73.337.4035.0 | bottom BAS GUT GD 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M32 on the right side (IP54), low version, 16-polig                   |
| 73.337.4035.1 | bottom BAS GUT GD 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the right side, low version, 16-polig                        |
| 73.338.4035.1 | bottom BAS GUT GB 16H M40 A1   | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the right and left side, low version, 16-polig               |
| 73.339.4035.0 | bottom BAS GUT GC 16H M40 A0   | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M40 on the left side (IP54), low version, 16-polig                    |
| 73.339.4035.1 | bottom BAS GUT GC 16H M40 A1   | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the left side, low version, 16-polig                         |
| 73.340.4035.0 | bottom BAS GUT GB 16H M40 A1   | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the right and left side, low version, 16-polig               |
| 73.340.4035.1 | bottom BAS GUT GF 16HM25 50 A1 | Bottom-base revos basic made of aluminum, for double locking lever with threaded hole M25 on the left and right side, with protective cover, low version, 16-polig      |
| 73.341.4035.0 | bottom BAS GUT GC 16H M40 A1   | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the left side, low version, 16-polig                         |
| 73.341.4035.1 | bottom BAS GUT GG 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M25 on the left side, with protective cover, low version, 16-polig                |
| 73.342.4035.0 | bottom BAS GUT GH 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever and cable gland M25 on the right side, with protective cover (IP54), low version, 16-polig          |
| 73.342.4035.1 | bottom BAS GUT GH 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M25 on the right side, with protective cover, low version, 16-polig               |
| 73.343.4035.0 | bottom BAS GUT GI 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever and cable gland M25 on the bottom, with protective cover (IP54), low version, 16-polig              |
| 73.343.4035.1 | bottom BAS GUT GI 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M25 on the bottom, with protective cover, low version, 16-polig                   |
| 73.344.4035.0 | bottom BAS GUT GF 16HM32 50 A0 | Bottom-base revos basic made of aluminum, for double locking lever with cable gland M32 on the left and right side, with protective cover (IP54), low version, 16-polig |
| 73.344.4035.1 | bottom BAS GUT GF 16HM32 50 A1 | Bottom-base revos basic made of aluminum, for double locking lever with threaded hole M32 on the left and right side, with protective cover, high version, 16-polig     |
| 73.345.4035.0 | bottom BAS GUT GG 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever and cable gland M32 on the left side, with protective cover (IP54), low version, 16-polig           |
| 73.345.4035.1 | bottom BAS GUT GG 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M32 on the left side, with protective cover, low version, 16-polig                |
| 73.346.4035.0 | bottom BAS GUT GH 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever and cable gland M32 on the right side, with protective cover (IP54), low version, 16-polig          |
| 73.346.4035.1 | bottom BAS GUT GH 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M32 on the right side, with protective cover, low version, 16-polig               |
| 73.347.4035.0 | bottom BAS GUT GI 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever and cable gland M32 on the bottom, with protective cover (IP54), low version, 16-polig              |
| 73.347.4035.1 | bottom BAS GUT GI 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever and threaded hole M32 on the bottom, with protective cover, low version, 40-polig                   |

