

product data sheet

item no. 71.472.1037.1

hood BAS GOM GL10 M20 B1

Hood revos basic metal-series without coating, with single locking lever and threaded hole B1 on the top - free cable connection, low version,M2-poles



item no.	71.472.1037.1
EAN	4049088461088
order unit	1 piece(s)

certificates / approvals



technical data

general

housing material	aluminum
color	grey
surface	bare
degree of protection (IP)	IP65
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	10
locking mechanism	single locking lever
cable entry	above
type of cable	thread
with cable screw gland	no
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	90.7 mm
width	43 mm
height	55 mm

