product data sheet

item no. 83.040.0130.1

IP switch WIENET UMS 5G-L

Unmanaged switch with 5 gigabit ethernet (10/100/1000 Mbit/s) ports, narrow version, plastic-housing



item no.	83.040.0130.1
EAN	4049088601125
order unit	1 piece(s)

certificates / approvals

c UL us LISTED

technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	plastic
manageable	no
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
Gigabit Ethernet	yes
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 10/100/1000 Mbps RJ45	5
number of ports 100 Mbps SC	0
type of electric connection	push-In connection//true
LED status indication	PWR1, PWR2, Alarm
connector cross section	0.25mm²...2.5mm² (AWG26...AWG12)
wire strip length	9 mm

technical data

voltage type	DC
min. operating temperature	0 °C
max. operation temperature	60 °C
storage temperature / transport min.	-20 °C
storage temperature / transport max.	70 °C
relative humidity min.	5 %
relative humidity max.	95 %
net weight	110 g
redundant power supply	2 power inputs


supply circuit

voltage type	DC
operating voltage min.	12 V
operating voltage max.	48 V

dimensions

depth	72 mm
width	25 mm
height	94 mm
weight	110 g

technical drawing



Qu – PEE 12/92

Teile-Nr. / Part-No.	Typ / Type
83.040.0129.1	UMS 5-L
83.040.0130.1	UMS 5G-L

Weitere Angaben siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.	www.wieland-electric.com eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed	1. Verwendung: First Use:	Blatt: Sheet:

	Tag/ Date	Name
2020		
gezeichnet drawn	15.12.	Koetzner
geprüft checked		
Normgepr. Stand. check		

Werkstoff/ Material

Maßstab/Scale

Zeichnung Nr./ Drawing No.

T 83.040.0129.1 01K

Maße in mm/Dimensions are in mm

Datei/ File: 047321__01K.DCD

Ersatz für/ Replacement for:

Index	Datum/ Blatt Date/ Sheet
Änderung/ Revision	

wieland
www.wieland-electric.com

Type

Benennung/ Title

Teilespezifikation /
Component specification

WIENET IP SWITCH