product data sheet

item no. 05.569.7453.0

cable clip FLATCABLE SCREW

Cable clip for podis® CON and gesis® NRG flatcables, for all cross- sections; for effective installation using quick-release fastener and just one fixing point; Version for fixing with screw; for wall and ceiling mount; with clips for the installation to cable trays with 25 mm mounting distance; color black



item no.	05.569.7453.0
EAN	4049088663109
order unit	100 piece(s)

certificates / approvals

technical data

general

material	plastic
UV resistant	yes

dimensions

length	87 mm
assembly width	23.5 mm
assembly height	30 mm

accessories

item no.	type	description
05.569.7753.0	Clip Basket FLATCABLE	Accessory for easy installation of cable clips 05.569.7453.0 and 05.569.7453.0 on mesh cable trays with grid 25 mm / 35 mm / 40 mm / 50 mm. Includes clip and corresponding screw.
F0.000.0055.7	Pipe Clamp D20	Pipe clip for installation tubes diameter 20 mm; compatible with cable clips 05.569.7453.0 and 05.569.7553.0
F0.000.0056.3	Pipe Clamp D25	Pipe clip for installation tubes diameter 25 mm; compatible with cable clips 05.569.7453.0 and 05.569.7553.0
F0.000.0056.4	Pipe Clamp D32	Pipe clip for installation tubes diameter 32 mm; compatible with cable clips 05.569.7453.0 and 05.569.7553.0
F0.000.0056.5	Pipe Clamp D40	Pipe clip for installation tubes diameter 40 mm; compatible with cable clips 05.569.7453.0 and 05.569.7553.0
F0.000.0056.6	Pipe Clamp D50	Pipe clip for installation tubes diameter 50 mm; compatible with cable clips 05.569.7453.0 and 05.569.7553.0

technical drawing









Hinweis
/note

(1) Kabeldicke min. 6mm
/cable thickness min. 6mm
Kabeldicke max. 12mm
/cable thickness max. 12mm

Bestellnummer /order number	Typ /type
05.569.7453.0	podis

Weitere Daten diehe KATALOG oder eKATALOG /additional data see CATALOG or eCATALOG	www.wieland-electric.com eshop.wieland-electirc.com

Toleranzierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (List of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: Sheet: 1 von of 1

Werkstoff / Material

Maßstab / Scale 1:1

	Tag/Date	Name
gezeichnet (drawn)	21.11.2023	Gähl M.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No. 05.569.7453.0 13K

Index -

Maße in mm / Dimensions are in mm

Vol. mm³ Qfl./Srf. mm²

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland

Type podis

Benennung/Title
BEFESTIGUNGSSCHELLE SCHRAUB
FIXING CLIP SCREW

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction of this document and communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only injection dimensions

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße

2023-11-21 09:58:00 1.000

01-QU-RD-32/21