
product data sheet

item no. 0D.S51.3327.0

insert bridge IVB WTN 150-3 IN

insert bridge IVB WTN 150-3 IN modular spacing 31 mm, insulated yes, number of poles 3, color grey, height 39.6 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0



item no.	0D.S51.3327.0
EAN	4049088724053
order unit	50 piece(s)


certificates / approvals


technical data


general

color	grey
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	85.6 mm
length	44.5 mm
modular spacing	31 mm
number of bridged clamps	3
mounting method	screwable
insulated	yes
model	cross connector
height	39.6 mm

technical drawing







© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
confidentiality class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe KATALOG oder eKatalog | www.wieland-electric.com
additional data see CATALOG or eCATALOG | eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 2:1

	Tag/Date	Name
gezeichnet / drawn	29.10.2025	Eichhorn N.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.S51.3227.0 13K

Index

Maße in mm / Dimensions are in mm

Vol. mm³ | Ofl./Srf. mm²

Ersatz für / Replacement for:

Type

Benennung/Title: EINLEGEBRUECKE
connection plug

wieland

Index | Datum / Blatt Date / Sheet | Änderung / Revision

Bestell-Nr. /order no.	Polzahl P /number of poles P	Typ /type	Farbe /colour	VPE: packaging unit:
0D.S51.3227.0	2	IVB WTN 150-2 IN	grau / grey	50
0D.S51.3327.0	3	IVB WTN 150-3 IN	grau / grey	