product data sheet

item no. 0D.S08.4027.0

jumper bar IVB WTN 6-10 S

jumper bar IVB WTN 6-10 S modular spacing 8 mm, insulated yes, number of poles 10, color grey, height 24 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0



item no.	0D.S08.4027.0
EAN	4049088723544
order unit	50 piece(s)


certificates / approvals


technical data


general

color	grey
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	78.2 mm
length	10.5 mm
modular spacing	8 mm
number of bridged clamps	10
mounting method	screwable
insulated	yes
model	cross connector
height	24 mm

technical drawing







© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
Confidentiality Class: Confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe KATALOG oder eKatalog | www.wieland-electric.com
additional data see CATALOG or eCATALOG | eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 5:1

	Tag/Date	Name
gezeichnet / drawn	15.10.2025	Eichhorn N.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.S08.3227.0 13K

Index

Maße in mm / Dimensions are in mm

Vol. mm³ | Ofl./Srf. mm²

Ersatz für / Replacement for:

Bestell-Nr. /order no.	Typ /type	Farbe /colour
0D.S08.3227.0	IVB WTN 6-2 S	grau / grey
0D.S08.4027.0	IVB WTN 6-10 S	grau / grey

wieland

Type

Benennung/Title

VERBINDUNGSSTEG

jumper bar

Index | Datum / Blatt Date / Sheet | Änderung / Revision

2025-11-26 15:37:22 1.000

01-QU-RD-32/21