
product data sheet

item no. 0D.204.5027.5

jumper bar IVB WTPN 4-20

jumper bar IVB WTPN 4-20 modular spacing 6.1 mm, insulated yes, number of poles 20, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0



item no.	0D.204.5027.5
EAN	4049088731686
order unit	100 piece(s)


certificates / approvals


technical data


general

color	red
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	120.4 mm
length	3 mm
modular spacing	6.1 mm
number of bridged clamps	20
mounting method	pluggable
insulated	yes
model	cross connector
height	23 mm

technical drawing







Bestell-Nr. /order no.	Polzahl P /number of poles P	Typ /type	Farbe /colour
0D.204.3227.5	2	IVB WTPN 4-2	rot / red
0D.204.3327.5	3	IVB WTPN 4-3	rot / red
0D.204.3427.5	4	IVB WTPN 4-4	rot / red
0D.204.3527.5	5	IVB WTPN 4-5	rot / red
0D.204.4027.5	10	IVB WTPN 4-10	rot / red
0D.204.5027.5	20	IVB WTPN 4-20	rot / red

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG
www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: Sheet: 1 von of 1

Index / Änderung / Revision / Datum / Blatt Date / Sheet

Maßstab / Scale 5:1

Werkstoff / Material

Vol. mm³ Ofl./Srf. mm²

gezeichnet drawn: Tag/Date 10.02.2025 Name Hollet

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.204.3227.5 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

wieland

Type

Benennung/Title
VERBINDUNGSSTECKER
connection plug

© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
Confidentiality Class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

2025-11-26 10:37:56 1.000

01-QU-RD-32/21