
product data sheet

item no. 0D.203.5327.5

jumper bar IVB WTPN 2.5 500

jumper bar IVB WTPN 2.5 500 modular spacing 5.1 mm, insulated yes, color red, height 10.7 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0



item no.	0D.203.5327.5
EAN	4049088731648
order unit	5 piece(s)


certificates / approvals


technical data

general

color	red
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	500 mm
length	2.15 mm
modular spacing	5.1 mm
number of bridged clamps	60
mounting method	pluggable
insulated	yes
model	cross connector
height	10.7 mm
halogen free	yes

technical drawing





© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
Confidentiality Class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 5:1

	Tag/Date	Name
gezeichnet / drawn	30.10.2025	Eichhorn N.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.203.5227.5 13K
Index: a

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Type

Benennung/Title: VERBINDUNGSSTECKER
jumper bar

Index	Datum / Blatt Date / Sheet	Änderung / Revision
a	16.04.2026 /	

wieland

Bestell-Nr. /order no.	Länge L /lenght L	Typ /type	Farbe /colour
0D.203.5227.5	50	IVB WTPN 2.5 50	rot / red
0D.203.5327.5	500	IVB WTPN 2.5 500	rot / red

2026-04-16 10:09:01 1.000

01-QU-RD-32/21