product data sheet

item no. 0D.203.5227.5

# jumper bar IVB WTPN 2.5 50

jumper bar IVB WTPN 2.5 50 modular spacing 5.1 mm, insulated yes, number of poles 50, color red, height 10.7 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0



| | |
|---|---|
| item no. | 0D.203.5227.5 |
| EAN | 4049088731631 |
| order unit | 20 piece(s) |


## certificates / approvals


## technical data

**general**

| | |
|---|---|
| color | red |
| inflammability class of insulation material acc. with UL94 | V0 |
| width/grid dimension | 50 mm |
| length | 2.15 mm |
| modular spacing | 5.1 mm |
| number of bridged clamps | 6 |
| mounting method | pluggable |
| insulated | yes |
| model | cross connector |
| height | 10.7 mm |
| halogen free | yes |

technical drawing




© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
Confidentiality Class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 5:1

| | Tag/Date | Name |
|---|---|---|
| gezeichnet / drawn | 30.10.2025 | Eichhorn N. |

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.203.5227.5 13K
Index: a

Maße in mm / Dimensions are in mm

Vol. mm³ | Ofl./Srf. mm²

Ersatz für / Replacement for:

Type

Benennung/Title: VERBINDUNGSSTECKER
jumper bar

| Index | Datum / Blatt Date / Sheet |
|---|---|
| a | 16.04.2026 / |
| Änderung / Revision | |

wieland

| Bestell-Nr. /order no. | Länge L /lenght L | Typ /type | Farbe /colour |
|---|---|---|---|
| 0D.203.5227.5 | 50 | IVB WTPN 2.5 50 | rot / red |
| 0D.203.5327.5 | 500 | IVB WTPN 2.5 500 | rot / red |

2026-04-16 10:09:01 1.000

01-QU-RD-32/21