
product data sheet

item no. 0D.ST0.0855.0

end bracket WEFN 8 TS15

end bracket WEFN 8 TS15 length 25.2 mm, height 26.2 mm, mounting method DIN rail (top hat rail), color grey, inflammability class of insulation material acc. with ul94 V0, terminal blocks for electrical installations yes



item no.	0D.ST0.0855.0
EAN	4049088732140
order unit	50 piece(s)

certificates / approvals

technical data


general

color	grey
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	8 mm
latching	screwable
length	25.2 mm
mounting method	DIN rail (top hat rail)
height	26.2 mm
Reihenklemmen für Installationsverteiler	yes


accessories


item no.	type	description
0D.206.7056.0	marking plate WMP 8-10	marking plate WMP 8-10 modular spacing 8 mm, material plastic, color white, length 128 mm, height 76 mm, inflammability class of insulation material acc. with ul94 V0

technical drawing



Hutschiene EN 60715-15x5,5
/mounting rail EN 60715-15x5,5





© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: vertraulich
confidentiality class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With (E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit (E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG
www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 2:1

Vol. mm³ Ofl./Srf. mm²

	Tag/Date	Name
gezeichnet / drawn	14.10.2025	Eichhorn N.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.ST0.0855.0 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Bestell-Nr. /order no.	Typ /type	Farbe /colour	VPE: packaging unit:
0D.ST0.0855.0	WEFN 8 TS15	grau / grey	50

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland

Type

Benennung/Title

ENDKLAMMER

end bracket

2025-11-18 14:31:15 1.000

01-QU-RD-32/21