product data sheet

item no. 0D.S06.5955.5

test plug PS 6 WTN RT

test plug PS 6 WTN RT number of clamp positions per level 1, mounting method pluggable, color red, width/grid dimension 10.9 mm, inflammability class of insulation material acc. with ul94 V0



item no.	0D.S06.5955.5
EAN	4049088723407
order unit	250 piece(s)

certificates / approvals

technical data

general

color	red
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	10.9 mm
length	10.9 mm
mounting method	pluggable
height	56.8 mm
wire strip length	6 mm
Anzahl der Klemmstellen je Etage	1

accessories


wire strip length	6 mm

technical drawing

© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
confidentiality class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig



Weitere Daten siehe KATALOG oder eKatalog | www.wieland-electric.com
additional data see CATALOG or eCATALOG | eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 2:1

	Tag/Date	Name
gezeichnet / drawn	31.10.2025	Eichhorn N.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 0D.S06.5955.1 13K

Index

Maße in mm / Dimensions are in mm

Vol. mm³ | Ofl./Srf. mm²

Ersatz für / Replacement for:

Type

Benennung/Title: PRUEFSTECKER
test plug

Index	Datum / Blatt Date / Sheet	Änderung / Revision
/		
/		
/		
/		
/		
/		
/		

wieland

Bestell-Nr. /order no.	Typ /type	Farbe /colour
0D.S06.5955.1	PS 6 WTN SW	schwarz / black
0D.S06.5955.5	PS 6 WTN RT	rot / red

2025-11-26 15:18:56 1.000

01-QU-RD-32/21