
product data sheet

item no. 0D.203.0155.0

end bracket WEFN 2.5 PE

end bracket WEFN 2.5 PE length 68.5 mm, height 43.5 mm, mounting method DIN rail (top hat rail), color grey, inflammability class of insulation material acc. with ul94 V0, terminal blocks for electrical installations yes



item no.	0D.203.0155.0
EAN	4049088731587
order unit	10 piece(s)


certificates / approvals


technical data


general

color	grey
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	10.16 mm
length	68.5 mm
mounting method	DIN rail (top hat rail)
height	43.5 mm
Reihenklemmen für Installationsverteiler	yes

technical drawing







© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
confidentiality class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With (E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit (E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe KATALOG oder eKatalog	www.wieland-electric.com
additional data see CATALOG or eCATALOG	eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 2:1

	Tag/Date	Name
gezeichnet / drawn	03.11.2025	Eichhorn N.

Elektronische Freigabe / Electronic Release

Zeichnung Nr. / Drawing No.: 0D.203.0155.0 13K

Index

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm² Ersatz für / Replacement for:

Type

Benennung/Title: ENDKLAMMER
end bracket

wieland

Index / Datum / Blatt Date / Sheet / Änderung / Revision

Bestell-Nr. /order no.	Typ /type	Farbe /colour	VPE: packaging unit:
0D.203.0155.0	WEFN 2.5 PE	grün-gelb / green-yellow	10

2025-11-20 09:26:19 1.000

01-QU-RD-32/21