product data sheet

item no. Z7.282.6629.0

jumper bar IVB WKN 6TK-6

Cross connector, insulated for DIN rail terminal blocks type WKN 6 TK..., 6 -pole



item no.	Z7.282.6629.0
EAN	4015573992528
order unit	10 piece(s)

certificates / approvals

technical data

general

color	yellow
modular spacing	8 mm
number of bridged clamps	6
mounting method	screwable
insulated	yes
model	cross connector

technical drawing



Teile-Nr. part-no.	Polzahl poles	L	T
Z7.282.6229.0	2	13,80	7,95
Z7.282.6329.0	3	21,75	15,90
Z7.282.6429.0	4	29,70	23,85
Z7.282.6529.0	5	37,65	31,80
Z7.282.6629.0	6	45,60	39,75

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach VU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document VU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz noch
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: -
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff/Material

	Tag/Date	Name
2013		
gezeichnet drawn	13.09.	Treschan
geprüft checked	-	-
Normgepr. Stand. check	-	-

Maßstab/Scale: 2:1

Zeichnung Nr./Drawing No.: Z7.282.6229.0 01K

Index: T

Maße in mm/Dimensions are in mm

Vol. mm³ Oft./Surf. mm²

Ersatz für/Replacement for: -

wieland
Elektrische Verbindungen

Type: IVB WKN 6TK ...

Benennung/Title
VERBINDUNGSSTEG
mit Schraube
jumper bar with screw

Index | Datum / Blatt Date / Sheet
Änderung/Revision

QU-PEM-08/91b

Z7282622901K_2 CADM3028 Treschan 2013-09-16T08:50:35 1.000