

product data sheet

item no. 96.032.4053.1

connector RST20I3S S1 ZR1 V SW

RST® CLASSIC connector, straight, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier black



item no.	96.032.4053.1
EAN	4015573769700
order unit	100 piece(s)

certificates / approvals



technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.
------	---

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
marking of poles	L, N, PE
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	9005

connection data

cable diameter max.	10 mm
cable diameter min.	6 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	male
connection type	screw connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69
---------------------------	-----------------------

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.271 kWh/St
insulation components continuous temperature	100 °C
surface finish	silver-plated

dimensions





length	79.1 mm
width	34.6 mm
height	34.6 mm

accessories


item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black

assembly

item no.	type	description
96.030.0153.1	distributor RST20i3V 3P1 F V SW	RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 3, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black
96.031.5053.1	device connector RST20i3S B1 M01 SW	RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.031.4053.1	connector RST20i3S B1 ZR1 SW	RST® CLASSIC connector, straight, number of poles 3, female, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier black
96.031.6153.1	device connector RST20i3S B1 M03 SW	RST® CLASSIC device connector, modular, straight, M16, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.031.6053.1	device connector RST20i3S B1 M00 SW	RST® CLASSIC device connector, modular, straight, M20, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.033.6053.1	device connector RST20i3S B1 M90 SW	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.035.6153.1	device connector RST20i3S B1 M13 SW	RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black



Schnitt A-A
section A-A



Verpackungseinheit: je 100 Stück
packaging unit: per 100

Teile-Nr./ part-nr.	Farbe:/ color:	Einz.-Tl.-Nr.: *)/ single-part-nr.:*)	Freitoleranz nach			CAD - Zeichnung, keine manuellen Änderungen			1.Verwendung: -		Bl.: 1 von 1	
				/	Maßstab	Werkstoff und Oberfläche: material and surface: Farbe: siehe Tabelle color: look table	2004	Tag	Name		Zeichnung Nr.	Index
96.032.4053.1	schwarz, ähnl. RAL 9005/ black, similar to RAL 9005	1		/	1:1			Entworfen	27.02.	Kneitz	T	96.032.4053.0 01K a
				/				Geprüft	-	-		
				/	Vel.	mm²	Bil.	mm²	Normgepr.	-	-	Ersatz für: -
				/								
96.032.4053.0	lichtgrau, ähnl. RAL 7035/ lightgrey, similar to RAL 7035	0	a	10.05.2005/		wieland			Type	Benennung		
			Buchstabe	Datum / Blatt		Elektrische Verbindungen			RST2013	STECKERTEIL MIT ZUGENTLASTUNG		
			Änderung						S S1 ZR1 V	male connector with cord grip screw-connection without wire protection/Schraubanschluß ohne Drahtschutz		