product data sheet

item no. 56.395.0155.0

feed-through terminal RFK 1 / 95 K S35/V0

Feed-through terminal with Screw connection for mounting on TS 35/7,5 mm, nominal cross section: 95 mm², width: 32 mm, color: grey



item no.	56.395.0155.0
EAN	4015573598546
order unit	10 piece(s)

certificates / approvals

technical data

general

nominal cross section	95 mm²
color	grey
number of levels	1
number of clamp positions per level	2
width/grid dimension	32 mm
insulating housing	PA666
inflammability class of insulation material acc. with UL94	V0
explosion-tested version "Ex e"	no
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	no
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 35/7.5 mm
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	no

technical data

rated current	250 A
rated voltage	1000 V
pollution degree	3
closing plate required	no
type of insulation material	thermoplastic
length	92 mm

connection data

connection type 1	screw connection
connection type 2	screw connection

minimum cross section fine stranded	16 mm²
maximum cross section fine stranded	95 mm²
minimum cross section stranded	16 mm²
maximum cross section stranded	95 mm²
wire strip length	27 mm
torque conductor mounting	10 Nm

technical data UL/CSA

cross section UL	6-3/0 AWG
voltage UL	600 V
current factory wiring	200 A
current field wiring	200 A
cross section CSA	6-3/0 AWG
voltage CSA	600 V
current CSA	200 A

technical drawing

