
product data sheet

item no. 73.335.6435.1

bottom BAS GUT GC 24HM32 50 A1

Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the left side, high version, 24- polig



item no.	73.335.6435.1
EAN	4015573623361
order unit	1 piece(s)

certificates / approvals

technical data

general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model


construction	24H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	sideways
type of cable	thread
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	144 mm
width	57 mm
height	80 mm

technical drawing

Ausführung .0
version .0








Weitere Daten siehe Katalog
further data see catalog

Teile - Nr. part - no.	Typ type
73.335.6435.0	BAS GUT GC 64HM32 50 A0
73.335.6435.1	BAS GUT GC 64HM32 50 A1



Ausführung .1
version .1

Toleranz nach DIN 7167/Tolerance system acc. to DIN 7167.
[This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances].

ja/yes ☒ Stoffverbots- und Deklarationsliste nach VU-TGM-05/03 ist einzuhalten. Conformity with Wieland document VU-TGM-05/03 [list of prohibited / declarable hazardous substances] to be declared!

Freitoleranz nach General tolerance: -

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: 1 Sheet: 1 von of 1

Werkstoff/Material

Maßstab/Scale: %

	Tag/Date	Name
2006		
gezeichnet drawn	27.10.	Treschan
geprüft checked	-	-
Normgeprüft Stand. check	-	-

Zeichnung Nr./Drawing No.: T 73.335.6435.0 01K

Index

Maße in mm/Dimensions are in mm

Vol. mm³ Oft./Surf. mm²

Ersatz für/Replacement for: -

Index / Datum / Blatt / Date / Sheet / Änderung/Revision

wieland
Elektrische Verbindungen

Type

Benennung/Title

GEHAEUSEUNTERTEIL

Closed housing

Gr. 64 M32 1x links / 1x left

OU-PEM-08/91

73335643501K_4 G4W1044 treschan 2006-10-27T10:07:13 1.000

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.