

Certification Record | CSA Group.

[Back to Product List \(/testing-certification/product-listing/\)](#)

CUSTOMER	CLASS	FILE NUMBER
Wieland Electric GmbH Brennerstrasse 10-14 Bamberg Bavaria Germany 96052	2258-02 (/testing-certification/product-listing/class/?class=2258-02) PROCESS CONTROL EQUIPMENT - For Hazardous Locations	012722_0_000

Class I, Zone 1, Ex e II T6

Terminal Blocks

"Selos"

Model(s)	Voltage (V)	Current (A)
Type WK 2,5 /U	600	25
Type WK 4 / U	600	40
Type WK 4/D1/2/U, Type WK 4 D2/2/U, Type WK 4/ D E/U	600	30
Type WK 4 E/U	300	10
Type WK 6/U	600	45
Type WKN 10/U	600	70
Type WKN 16/U	600	95
Type WKN 35/U	600	110
Type WKN 70/U	600	170

Model(s)	Voltage (V)	Current (A)
Type WKC 1/35, Type WKC 1 D1/2/35	600	13
Type WKC 2,5/35, Type WKC 2,5 D1/2/35	600	20

Class I, Zone 1, Ex e II T6

Taris

Model(s)	Voltage (V)	Current (A)
Type WKC 1 D2/2/35, Type WKC 1 E/35	300/600*	13
Type WKC 2,5 D2/2/35, Type WKC 2,5 E/35	300/600*	20

* with intermediate plate Type TWC 1-2,5 D2/E

To the requirements of
CAN/CSA-E60079-7-03, CAN/CSA-E60079-0-02

SUBJECT Ex e II T6 "fasis PRO" Series Terminal Blocks Type:

Model(s)	Voltage (V)	Current (A)	Spacing Group	Remarks
WKF 2.5 /35, WKF 2.5 D1/2/35, WKF 2.5 D2/2/35, WKF 2.5 D/D/35	600 max	25	-	Leg: 396 01/11, 396 02/12, 396 03/13, 396 04/14, 396 05/15, 396 06/16, 396 07/17, 396 08/18
WKF 4/35, WKF 4 D1/2/35	600 max	35	-	Leg: 396 01/11, 396 02/12, 396 03/13, 396 04/14, 396 05/15, 396 06/16, 396 07/17, 396 08/18
WKF 6/35	600 max	47	-	Leg: 396 01/11, 396 02/12, 396 03/13, 396 04/14, 396 05/15, 396 06/16, 396 07/17, 396 08/18
WKF 10/35	600 max	65	-	Leg: 396 01/11, 396 02/12, 396 03/13, 396 04/14, 396 05/15, 396 06/16, 396 07/17, 396 08/18
WKF 16/35	600 max	78	-	Leg: 396 01/11, 396 02/12, 396 03/13, 396 04/14, 396 05/15, 396 06/16, 396 07/17, 396 08/18

Model(s)	Voltage (V)	Current (A)	Spacing Group	Wire Range (AWG)	Remarks
WKFN 2.5 E/35, WKFN 2.5 E1/2/35, WKFN 2.5 E3/35	300 max	20	C	24-12	-
	600 max	20	E	24-12	-
	150	15	D	24-12	-
	300	10	D	24-12	-
	600 max	5	D	24-12	-

SL/35 (feed through terminal)	150	15	D	24-10	-
	300	10	D	24-10	-
	600	5	D	24-10	-
WKFN 4 E/35, WKFN 4 E/SL/35, WKFN 4 E/VB/35 (tier terminal block with index "E")	300 max	30	C and E	24-10	-
	150	15	D	24-10	-
	300 max	10	D	24-10	-

Contact an Expert
(<https://www.csagroup.org/contact>)

“fasis PRO” Protective Conductor Terminal Blocks Type:

Model(s)	Voltage (V)	Current (A)	Spacing Group	Wire Range (AWG)	Remarks
WKF 2.5 SL/35, WKF 2.5 D1/2/SL/35, WKF 2.5 D2/2/SL/35, WKF 4 SL/35, WKF 4 D1/2/SL/35, WKF 6 SL/35, WKF 10 SL/35, WKF 16 SL/35	600 max	-	C, D and E	-	Leg: 396 21, 396 22, 396 23, 396 24, 396 25, 396 26, 396 29, 396 30
WKFN 2.5 /SL/35, WKFN 2.5 D1/2/SL/35, WKFN 2.5 D2/2/SL/35, WKFN 2.5 E/SL/35, WKFN 2.5 E3/SL/35, WKFN 2.5 E1/2/SL/35	-	-	C, D and E	24-12	-

Contact an Expert

We’re always here to help. Let’s talk.

We’re here to answer your questions and help you get started right away. Call or send us a message anytime.

[Contact Us \(/contact\)](#)

(<https://www.csagroup.org>).

(<http://store.csagroup.org/ondemand-report/suspect-counterfeit>)

[language=en_US](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[Notices & Information Bulletins](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

([/notices-information-bulletins/](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[Submit an Incident Report](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

([/submit-a-report](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[Agreement on Acceptance of](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

[Components](http://store.csagroup.org/ondemand-report/suspect-counterfeit) ([/agreement-](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

[acceptance-components/](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[CSA Communities](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

([http://community.csagroup.org/login.jspx?](http://community.csagroup.org/login.jspx?login.jspx)

[referrer=%252Findex.jspx](http://community.csagroup.org/login.jspx?login.jspx))

[Marks](http://store.csagroup.org/ondemand-report/suspect-counterfeit) ([/testing-](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

[certification/marks-labels/brand-](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

[protection/reporting-suspect-](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

[counterfeit-marks](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[Resources & Insights](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

([/resources-insights/](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[Standards Research](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

([/standards/standards-research/](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

[CSA Group Product Listing](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

([/testing-certification/product-](http://store.csagroup.org/ondemand-report/suspect-counterfeit)

[listing/](http://store.csagroup.org/ondemand-report/suspect-counterfeit))

(<http://www.facebook.com/CSAGroup>)

(<http://www.linkedin.com/company/CSAGroup>)

(<http://www.youtube.com/channel/UC1351638321494>)

Contact an Expert
(<https://www.csagroup.org>)

[Legal](https://www.csagroup.org/legal/) (<https://www.csagroup.org/legal/>)

[Privacy Policy](https://www.csagroup.org/legal/privacy-policy/) (<https://www.csagroup.org/legal/privacy-policy/>)

[Evidence of Insurance](https://www.csagroup.org/legal/evidence-of-insurance/) (<https://www.csagroup.org/legal/evidence-of-insurance/>)

[HSSE Policy](https://www.csagroup.org/hsse-policy/) (<https://www.csagroup.org/hsse-policy/>)

[Accreditation](https://www.csagroup.org/accreditation/) (<https://www.csagroup.org/accreditation/>)

[Annual Report](https://www.csagroup.org/annual-report/) (<https://www.csagroup.org/annual-report/>)

[Accessibility](https://www.csagroup.org/accessibility/) (<https://www.csagroup.org/accessibility/>)

[Disclosures](https://www.csagroup.org/disclosures/) (<https://www.csagroup.org/disclosures/>)

© 2024 CSA Group Testing & Certification Inc. All rights reserved.