Product data sheet

Item No. 06.563.9053.0

Cover for female connector GL

RST16i5/4 cover piece, for covering unused female connectors, color light grey




Item No.	06.563.9053.0
EAN	4049088506420
Order Unit	100 Piece(s)

Certificates / Approvals

Technical drawing

gezeichnet: 2/3-polige Variante mit Verlierschutz

I drawn: 2/3 pole version with protection against loss



1:2

Teilenr./*part no.*	Pos.1	X	Y	Farbe/*colour*	Pole
06.563.9153.1	mit/*with*	20,2	23,45	schwarz/*black*	4/5
06.563.9153.0	mit/*with*	20,2	23,45	lichtgrau/*lightgrey*	4/5
06.563.9053.1	ohne/*without*	20,2	23,45	schwarz/*black*	4/5
06.563.9053.0	ohne/*without*	20,2	23,45	lichtgrau/*lightgrey*	4/5
06.563.8753.1	mit/*with*	16,3	22,75	schwarz/*black*	2/3
06.563.8753.0	mit/*with*	16,3	22,75	lichtgrau/*lightgrey*	2/3
06.563.8653.1	ohne/*without*	16,3	22,75	schwarz/*black*	2/3
06.563.8653.0	ohne/*without*	16,3	22,75	lichtgrau/*lightgrey*	2/3

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale 1:1

	Tag/Date	Name
gezeichnet drawn	16.10.2018	Hollet
geprüft checked		
Normgepr. Stand. check		

Zeichnung Nr. / Drawing No. T 06.563.8653.0 13K

Index

Maße in mm / Dimensions are in mm

Vol. mm³ Oft./Srf. mm² Ersatz für / Replacement for: Z6.561.68/6953.0/1

Index / Datum / Blatt / Date / Sheet / Änderung / Revision

wieland
www.wieland-electric.com

Type RST16

Bennenung/Title

VERSCHLUSSKAPPE

für Buchse mit/ohne Verlierschutz

cap for socket with/without protection against loss

06_563_8653_0_13K_sheet_2 CADW4030 Hollet 2018-10-19T08:29:13 1.000

QU-MEE-01/14 a