

product data sheet

item no. 83.040.1223.0

IP switch WIENET UMS 20-16G-4SFP-W

Unmanaged switch with 16 gigabit Ethernet (10/100/1000 Mbit/s) and 4 SFP ports, Wide-Temperature



item no.	83.040.1223.0
EAN	4049088600944
order unit	1 piece(s)

certificates / approvals



technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	metal
manageable	no
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
Gigabit Ethernet	yes
number of ports 10/100 Mbps RJ45	0
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 10/100/1000 Mbps RJ45	16
number of ports 100 Mbps SC	0
SFP ports	4
type of electric connection	screw connection
LED status indication	PWR1, PWR2, SYS, Alarm, LNK/ACT
connector cross section	0.35mm²...2.5mm²
wire strip length	8 mm

technical data

voltage type	DC
min. operating temperature	-40 °C
max. operation temperature	75 °C
storage temperature / transport min.	-40 °C
storage temperature / transport max.	85 °C
relative humidity min.	10 %
relative humidity max.	95 %

net weight	1100 g
redundant power supply	2 power inputs

supply circuit


voltage type	DC
operating voltage min.	12 V
operating voltage max.	48 V
power consumption max.	< 15 W

dimensions

depth	105 mm
width	74 mm
height	152 mm
weight	1100 g

Wieland's rights are reserved for the use of these documents. Vorverkauf und Mitverkauf
series rights and verboten. Serial rights and verboten. Serial rights and verboten. Serial rights
The introduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited

Qu - PEE 12/92



Weitere Angaben siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance		CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed			1. Verwendung: First Use:		Blatt: Sheet:	
			Werkstoff/ Material		2021	Tag/ Date	Name	
					gezeichnet drawn	22.02.	Koetznr	
		Maßstab/Scale	Elektronische Freigabe Electronic Release			Zeichnung Nr./ Drawing No. 83.040.1223.0 01K		
		Datei/ File: 047341__01K.DCD			Ersatz für/ Replacement for:			Maße in mm/Dimensions are in mm
		 wieland www.wieland-electric.com			Type	Benennung/ Title Teilespezifikation / Component specification WIENET IP SWITCH UMS 20-16G-4SFP-W		
Index	Datum/ Blatt Date/ Sheet							
Änderung/ Revision								

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
i
11.1
12.1
1.1