product data sheet

item no. 4L.020.0141.4

distributor RST08i2VL3P1HF V L SG

RST® MICRO distribution block 1I / 3O, rated voltage 50 V / 120 V, rated current 8 A, number of poles 2, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 3, pole codification 1, 2, color of coding/ contact carrier slate grey, ral number coding/contact insert



item no.	4L.020.0141.4
EAN	4049088557514
order unit	50 piece(s)

certificates / approvals

technical data

note

note	Please note the deviating continuous temperature resistance to the connector and device connector.Use only one connector with contact sealing - either male or female connector.

general

rated current	8 A
rated voltage	50 V / 120 V
rated impulse voltage	2.5 kV
pollution degree	3
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	slate grey
Pole codification	1, 2
RAL number coding/contact insert	7015

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	distribution block

material

housing material	TPU
halogen free	yes
contact material	CuZn
fire load	0.222 kWh/St
insulation components continous temperature	80 °C
surface finish	silver-plated

dimensions

length	50.6 mm
width	47.8 mm
height	22.8 mm


accessories


item no.	type	description
06.563.5053.1	cover for female connector SW	RST08i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
06.563.5153.1	cover for male connector SW	RST08i3/2 cover piece, for covering unused male connectors, with fastening belt, color black

















assembly

item no.	type	description
41.021.3041.4	connector RST08i3/2S B1 ZR1SHL SG	RST® MICRO connector, straight, number of poles 2, female, connection type screw connection, rated voltage 50 V / 120 V, rated current 8 A, cable diameter 4 - 7 mm, color of coding/ contact carrier slate grey
41.022.3041.4	connector RST08i3/2S S1 ZR1SHL SG	RST® MICRO connector, straight, number of poles 2, male, connection type screw connection, rated voltage 50 V / 120 V, rated current 8 A, cable diameter 4 - 7 mm, color of coding/ contact carrier slate grey


technical drawing





Teile-Nr. /part no.		
4L.020.0143.1		
4L.020.0143.9		
4L.020.0141.4		
4L.030.0153.1		
4L.030.0143.9		
4L.030.0141.4		
4L.020.0241.8		
4L.030.0351.8		

● = unbestückt / unpopulated



Teile-Nr. /part no.	Benennung /designation	Typ /type	Kodierungsfarbe /color of coding
4L.020.0143.1	H-PARALLEL-2pol-K1	RST08i2VL3P1HF V SW	schwarz / black
4L.020.0143.9	H-PARALLEL-2pol-K2	RST08i2VL3P1HF V BL	lichtblau / light blue
4L.020.0141.4	H-PARALLEL-2pol-K3	RST08i2VL3P1HF V L SG	schiefergrau / slate grey
4L.030.0153.1	H-PARALLEL-3pol-K1	RST08i3VL3P1HF V SW	schwarz / black
4L.030.0143.9	H-PARALLEL-3pol-K2	RST08i3VL3P1HF V BL	lichtblau / light blue
4L.030.0141.4	H-PARALLEL-3pol-K3	RST08i3VL3P1HF V L SG	schiefergrau / slate grey
4L.020.0241.8	H-SERIELL-2pol-K4	RST08i2VL3S1HF V L KG	kieselgrau / pebble grey
4L.030.0351.8	H-SERPAR-3pol-K4	RST08i3VL3G1HF V L KG	kieselgrau / pebble grey

Gezeichnete Ausführung: /drawn version:

Weitere Daten siehe KATALOG oder eKatalog / additional data see CATALOG or eCATALOG — www.wieland-electric.com / eshop.wieland-electric.com

Toleranz Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: First Use

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale 1:1

Vol. mm³ Oft./Srf. mm²

Ersatz für / Replacement for:

Maße in mm / Dimensions are in mm

	Tag/Date	Name
gezeichnet / drawn	19.02.2020	Hollet
geprüft / checked		
Norm gepr. / Stand. check		

Zeichnung Nr. / Drawing No.: T 4L.030.0153.1 13K — Index: b

Index	Datum / Blatt / Date / Sheet	Änderung / Revision
b	26.05.2021 /	
a	17.03.2020 /	

wieland
www.wieland-electric.com

Type: RST MICRO VB

Benennung/Title: VERTEILERBLOCK_H
distributor block

4L_030_0153_1_1K_sheet 1_1 CAD V5505 Hollet 2021-05-26T07:53:43 1.000

QU-MEE-01/14 a

Weitergabe sowie Vervielfältigung dieser Dokumente, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung vorbehalten. Transmission of this document as well as reproduction and communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With a marked dimension, an extra visit for control will be charged

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit x gekennzeichnete Maße sind nur für interne Kontrolle wichtig