product data sheet

item no. 83.041.0340.1

mobile Router WIENET LTE LR340 EMEA

wienet LTE LR340, 4G LTE Cat.4 VPN Security Router, robust metal housing for DIN-rail or wall mount, 2x SIM with cover, interfaces: 2x Ethernet 10/100 Mbit/s (independent IP), 1x RS232, 1x RS485, 1x I/O, 2x SMA<(>,<)> Power supply: 9-36 V DC, Configuration: Web server, VPN: openVPN, IPSec<(>,<)> L2TP, GRE, PPTP Network: DHCP, NAT/PAT, SSH, VRRP, PPPoE, SNMP, SMTP<(>,<)> Dyn DNS client, DNS proxy, VLAN, QoS, Backup Routes, Port Forwarding<(>,<)> Host Port Routing, Ethernet Bridging, Load Balancing, IPv6 Dual Stack<(>,<)> Control and diagnostics: SMS, email, SNMP Trap, Status, Features: Node-RED, MQTT, Operating temperature: -40 ... +75°C



item no.	83.041.0340.1
EAN	4049088653919
order unit	1 piece(s)

certificates / approvals

c UL US LISTED

technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	metal
port 1	ETH
port 2	ETH
LED status indication	PWR, USR, DI, DO, DAT, SIG, TECH, SIM

supply circuit

voltage type	DC
operating voltage min.	10 V
operating voltage max.	30 V
power consumption max.	leer 5.8 W

dimensions


depth	31.2 mm
width	129 mm
height	94 mm
weight	470 g

accessories

item no.	type	description
F0.000.0035.1	antenna WIENET ANTENNE 15863V2 DACH ANT.	wienet omni-roof antenna - Outdoor antenna, Frequency range: GSM/GPRS/EDGE/UMTS/ LTE/5G/LoRaWAN/NB-IoT, Profits: max. 7dBi, Connector: 1xSMA / M, Cable length: 5m, Dimensions:. 82x48x48mm, incl. bracket (pole and wall mounting)
F0.000.0035.2	antenna WIENET ANTENNE 15869V2 FAHRZEUG ANT.	"wienet Car Antenna v2 - 5dBi external antenna Frequency ranges: GSM / GPRS / EDGE / UMTS / LTE Supports MiMo and Diversity Profit: max. 5dBi Connector: 2x SMA / M 2 x Cable: 0.3m Dimensions: height 82mm, diameter 176mm Color: Black Roof installation"
F0.000.0037.6	antenna WIENET ANTENNE 15862V2 PANEL ANT.	"wienet panel antenna v2 - 5dBi external antenna Frequency ranges: GSM / GPRS / EDGE / UMTS / LTE MiMo and Diversity Antenna (lightweight microwave effect) Profit: max. 5dBi

		Connector: 2x SMA / M Cable length: 5m Dimensions: approx 155x155x75mm incl. Bracket (mast, wall and table mounting)"
F0.000.0037.8	antenna WIENET ANTENNE 15872V2 PANEL ANT.	"wienet Panel Antenna v2 - 9dBi outdoor antenna Frequency ranges: GSM / GPRS / EDGE / UMTS / LTE MiMo and Diversity Antenna with microwave effect Profit: max. 9dBi Connector: 2x SMA / M Cable length: 5m Dimensions: approx 180x200x94mm incl. Bracket (mast, wall and Table mounting)"
F0.000.0031.8	adapter MPI-ETH Adapter ACCON-NetLink-PRO compact	compact communication adapter to connect PC with S7-200/300/400 over TCP/IP. Up to 32 concurrent MPI- and PROFIBUS connections possible, automatic detecting of TCP rate (10/100 Mbit/s), Power supply 24 V DC extern.

technical drawing



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

01-QU-RD-31/21

Weitere Angaben siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.	www.wieland-electric.com eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed	1. Verwendung: First Use:	Blatt: Sheet:

Werkstoff/ Material	2022	Tag/ Date	Name
Maßstab/Scale	gezeichnet drawn	19.10.	Koetzner
Elektronische Freigabe Electronic Release			

Zeichnung Nr./ Drawing No.
83.041.0340.1 01K
Maße in mm/Dimensions are in mm

Datei/ File: 047981__01K.DCD
Ersatz für/ Replacement for:

Index / Änderung/ Revision	Datum/ Blatt Date/ Sheet	
wieland	Type	Benennung/ Title: Teilespezifikation / Component specification WIENET LTE LR340 EMEA

2022-12-13 11:07:07 1.000