File E247489
Project 4790635028

December 20, 2023

REPORT

on

* Cable Assemblies and Fittings for Industrial Control and Signal Distribution

Wieland Electric Gmbh
Bamberg DE

Copyright © 2023 UL LLC

UL LLC authorizes the above named company to reproduce this Report only for purposes as described in the Conclusion, provided it is reproduced in its entirety.

DESCRIPTION

PRODUCT COVERED:

USL, CNL - Connector Module, Model FCS 4 7 SI FK, may be followed by FM.

RATINGS:

For the US only

Cat Nos.	Number of Poles Live/Ground	Conductors and Cable	Voltage (V ac)	Current (A)
FCS 4 7 SI FK and FCS 4 7 SI FK FM	6/1 - Output	No. 12 AWG, STR/SOL /Stranded with ultrasonic welding, Cu	600	20
	6/1 - Input	4mm2 TC-ER	600	20

For the US and Canada:

Cat Nos.	Number of Poles Live/Ground	Conductors and Cable	Voltage (V)	Current (A)
FCS 4 7 SI FK and FCS 4 7 SI FK FM	6/1 - Output	No. 12-14 AWG, STR/SOL/Stranded with ultrasonic welding, Cu	600	15
	6/1 - Input	$4mm^2$ TC-ER	600	15

GENERAL:

* These modules are 6-pole, 7-wire connectors with ground and intended for wall mounting. They are assembled on $4mm^2$ Stranded TC-ER Ribbon Cable via insulation piercing contacts and on conductors via spring force terminals.

USL - Products designated USL have been investigated using US requirements as noted in the Test Record.

* CNL - Products designated USL have been investigated using Canadian requirements as noted in the Test Record.

*