
product data sheet

item no. 5D.204.0055.6

feed-through terminal WTPN 4 BL

feed-through terminal WTPN 4 BL rated voltage 800 V, rated current 32 A, push-In connection//true, number of levels 1, number of clamp positions per level 2, nominal cross section 4 mm², connectable conductor cross section fine stranded without cable end sleeve 0,2mm² - 4mm², mounting method DIN rail (top hat rail), color blue, width/grid dimension 6.1 mm, inflammability class of insulation material acc. with ul94 V0, terminal blocks for electrical installations yes



item no.	5D.204.0055.6
EAN	4049088706677
order unit	100 piece(s)

certificates / approvals

technical data

general

nominal cross section	4 mm²
color	blue
number of levels	1
number of clamp positions per level	2
width/grid dimension	6.1 mm
insulating housing	PA
inflammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)
terminal blocks for electrical installations	yes
Anschlussart	push-In connection//true
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail)
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes
halogen free	yes

technical data

rated current	32 A
rated voltage	800 V
rated impulse voltage	8 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	57 mm
width	6.1 mm
height	36.5 mm

connection data

connection type	push-In connection//true
connection type 1	plug-in connection

minimum cross section solid	0.2 mm²
maximum cross section solid	6 mm²
minimum cross section fine stranded	0.2 mm²
maximum cross section fine stranded	4 mm²
minumum conductor cross section (flex., stranded) with cable end sleeve	0.25 mm²
maximum conductor cross section (flex., stranded) with cable end sleeve	4 mm²
wire strip length	12 mm

technical data UL/CSA


cross section UL	24-10 AWG
voltage UL	600 V
current factory wiring	30 A
current field wiring	30 A
cross section CSA	24-10 AWG
voltage CSA	600 V
current CSA	30 A


accessories

item no.	type	description
0D.203.5127.5	jumper bar IVB WTPN 2.5R4	jumper bar IVB WTPN 2.5R4 modular spacing 5.6 mm, insulated yes, number of poles 2, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.3227.5	jumper bar IVB WTPN 4-2	jumper bar IVB WTPN 4-2 modular spacing 6.1 mm, insulated yes, number of poles 2, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.3327.5	jumper bar IVB WTPN 4-3	jumper bar IVB WTPN 4-3 modular spacing 6.1 mm, insulated yes, number of poles 3, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.3427.5	jumper bar IVB WTPN 4-4	jumper bar IVB WTPN 4-4 modular spacing 6.1 mm, insulated yes, number of poles 4, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.3527.5	jumper bar IVB WTPN 4-5	jumper bar IVB WTPN 4-5 modular spacing 6.1 mm, insulated yes, number of poles 5, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.4027.5	jumper bar IVB WTPN 4-10	jumper bar IVB WTPN 4-10 modular spacing 6.1 mm, insulated yes, number of poles 10, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.5027.5	jumper bar IVB WTPN 4-20	jumper bar IVB WTPN 4-20 modular spacing 6.1 mm, insulated yes, number of poles 20, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.5127.5	jumper bar IVB WTPN 1.5R4	jumper bar IVB WTPN 1.5R4 modular spacing 4.8 mm, insulated yes, number of poles 2, color red, height 23 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.5227.5	jumper bar IVB WTPN 4R6	jumper bar IVB WTPN 4R6 modular spacing 9.1 mm, insulated yes, number of poles 2, color red, height 30 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.5327.5	jumper bar IVB WTPN 4R10	jumper bar IVB WTPN 4R10 modular spacing 10.1 mm, insulated yes, number of poles 2, color red, height 36.1 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.5427.5	jumper bar IVB WTPN 4R16	jumper bar IVB WTPN 4R16 modular spacing 11.1 mm, insulated yes, number of poles 2, color red, height 37 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.204.8055.5	test plug PS 4	test plug PS 4 number of clamp positions per level 1, mounting method pluggable, color red, width/grid dimension 6.1 mm, inflammability class of insulation material acc. with ul94 V0
0D.204.8155.5	spacer SPS 4	spacer SPS 4 length 20 mm, height 27 mm, material plastic, color red, inflammability class of insulation material acc. with ul94 V0
0D.202.1055.0	partition TW 001	partition inflammability class of insulation material acc. with ul94 V0, type of end plate no, thickness 1.5 mm, length 57 mm, color grey
0D.204.2055.0	end plate APWTPN 4	end plate inflammability class of insulation material acc. with ul94 V0, type of end plate yes, thickness 2 mm, length 57 mm, color grey
0D.203.7455.0	marking tag ZS 003	marking tag ZS 003 modular spacing 5.1 mm, length 25 mm, height 22.4 mm, material plastic, color transparent, inflammability class of insulation material acc. with ul94 V0
0D.203.7555.0	marking tag ZS 004	marking tag ZS 004 modular spacing 12 mm, length 25 mm, height 22.4 mm, material plastic, color transparent, inflammability class of insulation material acc. with ul94 V0
0D.202.7281.0	marking strips WML 9.8/60	marking strips WML 9.8/60 material plastic, color white, length 230 mm, height 15.1 mm, inflammability class of insulation material acc. with ul94 V0
0D.202.7381.0	marking strips WML 7.4/60	marking strips WML 7.4/60 material plastic, color white, length 230 mm, height 11.4 mm, inflammability class of insulation material acc. with ul94 V0


0D.204.7056.0	marking plate WMP 6.10-10	marking plate WMP 6.10-10 modular spacing 6.1 mm, material plastic, color white, length 128 mm, height 76 mm, inflammability class of insulation material acc. with ul94 V0
0D.204.7156.0	marking plate WMP 6.10-5.8	marking plate WMP 6.10-5.8 modular spacing 6.1 mm, material plastic, color white, length 128 mm, height 76 mm, inflammability class of insulation material acc. with ul94 V0

technical drawing





1:1



Bestell-Nr. /order no.	Typ /type	Farbe /colour
5D.204.0055.0	WTPN 4	grau / grey
5D.204.0055.1	WTPN 4 SW	schwarz / black
5D.204.0055.2	WTPN 4 WS	weiß / white
5D.204.0055.4	WTPN 4 BR	weiß / white
5D.204.0055.5	WTPN 4 RT	rot / red
5D.204.0055.6	WTPN 4 BL	blau / blue
5D.204.0055.7	WTPN 4 GN	grün / green
5D.204.0055.8	WTPN 4 GE	gelb / yellow
5D.204.0055.9	WTPN 4 OR	orange

ⓐ

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG

www.wieland-electric.com
eshop.wieland-electric.com

Toleranz Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Maßstab / Scale 2:1

Werkstoff / Material

	Tag/Date	Name
gezeichnet drawn	10.02.2025	Hollet

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 5D.204.0055.0 13K

Index: a

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Index	Änderung / Revision	Datum / Blatt Date / Sheet
a		18.02.2026

wieland

Type

Benennung/Title

DURCHGANGSKLEMME

feed-through terminal

© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
Confidentiality class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With Ⓔ marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Ⓔ gekennzeichnete Maße sind nur für interne Zwecke gültig

2026-02-18 16:03:11 1.000

01-QU-RD-32/21