


product data sheet

item no. 0D.S92.2255.7

plug-in terminal WTN 1.5 PG02

plug-in terminal WTN 1.5 PG02 rated voltage 630 V, rated current 18 A, screw connection, number of levels 1, number of clamp positions per level 2, nominal cross section 1.5 mm², connectable conductor cross section fine stranded without cable end sleeve 0,2mm² - 2,5mm², mounting method DIN rail (top hat rail), color green, width/grid dimension 18 mm, inflammability class of insulation material acc. with UL94 V0, terminal blocks for electrical installations yes



item no.	0D.S92.2255.7
EAN	4049088724114
order unit	200 piece(s)

certificates / approvals

technical data

general

nominal cross section	1.5 mm ²
color	green
number of levels	1
number of clamp positions per level	2
width/grid dimension	18 mm
insulating housing	PA
inflammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)
terminal blocks for electrical installations	yes
Anschlussart	screw connection
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail)
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes

technical data

rated current	18 A
rated voltage	630 V
rated impulse voltage	4 kV
length	5.08 mm
width	10.16 mm
height	15 mm

connection data

connection type	screw connection
connection type 1	screw connection
minimum cross section solid	0.2 mm ²
maximum cross section solid	2.5 mm ²

minimum cross section fine stranded	0.2 mm ²
maximum cross section fine stranded	2.5 mm ²
minumum conductor cross section (flex., stranded) with cable end sleeve	0.25 mm ²
maximum conductor cross section (flex., stranded) with cable end sleeve	2.5 mm ²
wire strip length	8 mm
torque conductor mounting	0.5 Nm

technical data UL/CSA

cross section UL	28-12 AWG
voltage UL	300 V
current factory wiring	15 A
current field wiring	20 A
cross section CSA	28-12 AWG
voltage CSA	300 V
current CSA	15 A

