
product data sheet

item no. 5D.S04.4455.0

fuse terminal WTN 4 FSI5 5X20

fuse terminal WTN 4 FSI5 5X20 rated voltage 5 V, rated current 12 A, screw connection, number of levels 1, number of clamp positions per level 3, nominal cross section 4 mm², connectable conductor cross section fine stranded without cable end sleeve 0,34mm² - 4mm², mounting method DIN rail (top hat rail), color grey, width/grid dimension 8 mm, inflammability class of insulation material acc. with ul94 V0, terminal blocks for electrical installations yes



item no.	5D.S04.4455.0
EAN	4049088725067
order unit	50 piece(s)

certificates / approvals

technical data

general

nominal cross section	4 mm²
color	grey
number of levels	1
number of clamp positions per level	3
width/grid dimension	8 mm
insulating housing	PA
inflammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)
terminal blocks for electrical installations	yes
connection type	screw connection
number of clamp positions per level	3
mounting method	DIN rail (top hat rail)
inflammability class of insulation material acc. with UL94	V0
terminal blocks for electrical installations	yes
halogen free	yes

technical data

rated current	12 A
rated voltage	5 V
rated impulse voltage	6 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	53.3 mm
width	8 mm
height	47.3 mm

connection data

connection type	screw connection
connection type 1	screw connection
minimum cross section solid	0.34 mm²
maximum cross section solid	6 mm²
minimum cross section fine stranded	0.34 mm²
maximum cross section fine stranded	4 mm²
minumum conductor cross section (flex., stranded) with cable end sleeve	0.34 mm²
maximum conductor cross section (flex., stranded) with cable end sleeve	2.5 mm²
wire strip length	10 mm
torque conductor mounting	0.5 Nm


technical data UL/CSA


cross section UL	22-10 AWG
voltage UL	5 V
current factory wiring	12 A
current field wiring	12 A
cross section CSA	22-10 AWG
voltage CSA	5 V
current CSA	12 A


accessories


item no.	type	description
0D.S07.3227.0	insert bridge IVB WTN 6-2 IN	insert bridge IVB WTN 6-2 IN modular spacing 8 mm, insulated yes, number of poles 2, color grey, height 24.2 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S07.3327.0	insert bridge IVB WTN 6-3 IN	insert bridge IVB WTN 6-3 IN modular spacing 8 mm, insulated yes, number of poles 3, color grey, height 24.2 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S07.3427.0	insert bridge IVB WTN 6-4 IN	insert bridge IVB WTN 6-4 IN modular spacing 8 mm, insulated yes, number of poles 4, color grey, height 24.2 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S07.3527.0	insert bridge IVB WTN 6-5 IN	insert bridge IVB WTN 6-5 IN modular spacing 8 mm, insulated yes, number of poles 5, color grey, height 24.2 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S07.4027.0	insert bridge IVB WTN 6-10 IN	insert bridge IVB WTN 6-10 IN modular spacing 8 mm, insulated yes, number of poles 10, color grey, height 24.2 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S04.2455.0	end plate APWTN 4 FSI	end plate inflammability class of insulation material acc. with ul94 V0, type of end plate yes, thickness 1.2 mm, length 53 mm, color grey
0D.202.7281.0	marking strips WML 9.8/60	marking strips WML 9.8/60 material plastic, color white, length 230 mm, height 15.1 mm, inflammability class of insulation material acc. with ul94 V0
0D.206.7056.0	marking plate WMP 8-10	marking plate WMP 8-10 modular spacing 8 mm, material plastic, color white, length 128 mm, height 76 mm, inflammability class of insulation material acc. with ul94 V0

technical drawing









Bestell-Nr. /order no.	Typ /type	Farbe /colour
5D.S04.4355.0	WTN 4 FSI 5X20	grau / grey
5D.S04.4455.0	WTN 4 FSI5 5X20	grau / grey
5D.S04.4555.0	WTN 4 FSI12 5X20	grau / grey
5D.S04.4655.0	WTN 4 FSI24 5X20	grau / grey
5D.S04.4755.0	WTN 4 FSI48 5X20	grau / grey
5D.S04.4855.0	WTN 4 FSI110 5X20	grau / grey
5D.S04.4955.0	WTN 4 FSI220 5X20	grau / grey

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Maßstab / Scale: 2:1

Werkstoff / Material

Vol. mm³ Ofl./Srf. mm²

Tag/Date | Name
gezeichnet drawn | 16.09.2025 | Sachs (extern)

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 5D.S04.4355.0 13K
Index: a

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Type

Benennung/Title: SICHERUNGSKLEMME
fuse terminal

Index	Datum / Blatt Date / Sheet	Änderung / Revision
a	23.06.2026 /	

wieland

© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: confidentially class: Vertraulich confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

2026-07-01 07:17:15 1.000

01-QU-RD-32/21