
product data sheet

item no. 5D.S03.8755.0

multi-tier terminal WTN 2.5 E D02

multi-tier terminal WTN 2.5 E D02 rated voltage 250 V, rated current 0.5 A, screw connection, number of levels 2, number of clamp positions per level 2, nominal cross section 2.5 mm², connectable conductor cross section fine stranded without cable end sleeve 0,34mm² - 2,5mm², mounting method DIN rail (top hat rail), color grey, width/grid dimension 5.1 mm, inflammability class of insulation material acc. with ul94 V0



item no.	5D.S03.8755.0
EAN	4049088724817
order unit	20 piece(s)

certificates / approvals

technical data

general

nominal cross section	2.5 mm²
color	grey
number of levels	2
number of clamp positions per level	2
width/grid dimension	5.1 mm
insulating housing	PA
inflammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)
Anschlussart	screw connection
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail)
Brennbarkeitsklasse des Isolierstoffs	V0
halogen free	yes

technical data

rated current	0.5 A
rated voltage	250 V
rated impulse voltage	6 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	71.5 mm
width	5.1 mm
height	63 mm

connection data

connection type	screw connection

connection type 1	screw connection
connection type 2	screw connection
minimum cross section solid	0.34 mm²
maximum cross section solid	4 mm²
minimum cross section fine stranded	0.34 mm²
maximum cross section fine stranded	2.5 mm²
minumum conductor cross section (flex., stranded) with cable end sleeve	0.25 mm²
maximum conductor cross section (flex., stranded) with cable end sleeve	2.5 mm²
wire strip length	10 mm
torque conductor mounting	0.4 Nm

technical data UL/CSA





cross section UL	22-12 AWG
voltage UL	250 V
current factory wiring	0.5 A
current field wiring	0.5 A
cross section CSA	22-12 AWG
voltage CSA	250 V
current CSA	0.5 A

accessories


item no.	type	description
0D.S03.3227.5	jumper bar IVB WTN 2,5-2	jumper bar IVB WTN 2,5-2 modular spacing 5.1 mm, insulated yes, number of poles 2, color red, height 20.3 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S03.3327.5	jumper bar IVB WTN 2,5-3	jumper bar IVB WTN 2,5-3 modular spacing 5.1 mm, insulated yes, number of poles 3, color red, height 20.3 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S03.3427.5	jumper bar IVB WTN 2,5-4	jumper bar IVB WTN 2,5-4 modular spacing 5.1 mm, insulated yes, number of poles 4, color red, height 20.3 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S03.3527.5	jumper bar IVB WTN 2,5-5	jumper bar IVB WTN 2,5-5 modular spacing 5.1 mm, insulated yes, number of poles 5, color red, height 20.3 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S03.4027.5	jumper bar IVB WTN 2,5-10	jumper bar IVB WTN 2,5-10 modular spacing 5.1 mm, insulated yes, number of poles 10, color red, height 20.3 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S03.5027.5	jumper bar IVB WTN 2,5-20	jumper bar IVB WTN 2,5-20 modular spacing 5.1 mm, insulated yes, number of poles 20, color red, height 20.3 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S13.3227.5	jumper bar IVB WTN 2.5P2	jumper bar IVB WTN 2.5P2 modular spacing 10 mm, insulated yes, number of poles 2, color red, height 20.28 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S13.3327.5	jumper bar IVB WTN 2.5P3	jumper bar IVB WTN 2.5P3 modular spacing 10 mm, insulated yes, number of poles 3, color red, height 20.28 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S13.3427.5	jumper bar IVB WTN 2.5P4	jumper bar IVB WTN 2.5P4 modular spacing 10 mm, insulated yes, number of poles 4, color red, height 20.28 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S13.3527.5	jumper bar IVB WTN 2.5P5	jumper bar IVB WTN 2.5P5 modular spacing 10 mm, insulated yes, number of poles 5, color red, height 20.28 mm, mounting method pluggable, inflammability class of insulation material acc. with ul94 V0
0D.S23.3227.0	insert bridge IVB WTN 2.5-2 IN	insert bridge IVB WTN 2.5-2 IN modular spacing 5.1 mm, insulated yes, number of poles 2, color grey, height 19 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S23.3327.0	insert bridge IVB WTN 2.5-3 IN	insert bridge IVB WTN 2.5-3 IN modular spacing 5.1 mm, insulated yes, number of poles 3, color grey, height 19 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S23.3427.0	insert bridge IVB WTN 2.5-4 IN	insert bridge IVB WTN 2.5-4 IN modular spacing 5.1 mm, insulated yes, number of poles 4, color grey, height 19 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S23.3527.0	insert bridge IVB WTN 2.5-5 IN	insert bridge IVB WTN 2.5-5 IN modular spacing 5.1 mm, insulated yes, number of poles 5, color grey, height 19 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0
0D.S23.4027.0	insert bridge IVB WTN 2.5-10 IN	insert bridge IVB WTN 2.5-10 IN modular spacing 5.1 mm, insulated yes, number of poles 10, color grey, height 19 mm, mounting method screwable, inflammability class of insulation material acc. with ul94 V0


0D.S03.5955.5	test plug PS 2.5 WTN	test plug PS 2.5 WTN number of clamp positions per level 1, mounting method pluggable, color red, width/grid dimension 5.1 mm, inflammability class of insulation material acc. with ul94 V0
0D.S03.6955.9	lever LVWTN 2.5/4	lever LVWTN 2.5/4 length 13.2 mm, height 22.5 mm, material plastic, color orange, inflammability class of insulation material acc. with ul94 V0
0D.S03.2355.0	end plate APWTN 2.5/4 E	end plate inflammability class of insulation material acc. with ul94 V0, type of end plate yes, thickness 1.2 mm, length 70 mm, color grey
0D.S04.1055.9	partition TW 001 WTN	partition inflammability class of insulation material acc. with ul94 V0, type of end plate no, thickness 0.8 mm, length 15.8 mm, color grey
0D.202.7281.0	marking strips WML 9.8/60	marking strips WML 9.8/60 material plastic, color white, length 230 mm, height 15.1 mm, inflammability class of insulation material acc. with ul94 V0
0D.203.7056.0	marking plate WMP 5,10-10	marking plate WMP 5,10-10 modular spacing 5.1 mm, material plastic, color white, length 128 mm, height 76 mm, inflammability class of insulation material acc. with ul94 V0


technical drawing

5D.S03.8655.0	5D.S03.8755.0	5D.S03.8855.0	5D.S03.8955.0
			
WTN 2.5 E D01	WTN 2.5 E D02	WTN 2.5 E D03	WTN 2.5 E D04

Dargestellte Ansicht 5D.S03.8655.0
/shown version 5D.S03.8655.0







Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG
www.wieland-electric.com
eshop.wieland-electric.com

Bestell-Nr. /order no.	Typ /type	Farbe /colour
5D.S03.8655.0	WTN 2.5 E D01	grau / grey
5D.S03.8755.0	WTN 2.5 E D02	grau / grey
5D.S03.8855.0	WTN 2.5 E D03	grau / grey
5D.S03.8955.0	WTN 2.5 E D04	grau / grey

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).
ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (List of prohibited / declarable hazardous substances) to be declared!
Freitoleranz nach General tolerance
CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed
1. Verwendung: First Use:
Blatt: 1 von 1 Sheet: 1 of 1
Werkstoff / Material
Maßstab / Scale 2:1
Vol. mm³ Oft./Srf. mm²
Tag/Date Name
gezeichnet (drawn) 18.11.2025 Eichhorn N.
Elektronische Freigabe Electronic Release
Zeichnung Nr. / Drawing No. T 5D.S03.8655.0 13K
Index
Maße in mm / Dimensions are in mm
Ersatz für / Replacement for:
Index Datum / Blatt Date / Sheet
Änderung / Revision
wieland
Type
Benennung/Title
ETAGENKKLEMME
double deck terminal

2025-11-24 14:59:39 1.000
01-QU-RD-32/21