
product data sheet

item no. 25.330.3453.0

PCB pin header 8113 S / 4 G OB

PCB pin header, connection method depends on used socket part ,
4 poles, pitch: 5 mm, type of packing: carton, color: grey



item no.	25.330.3453.0
EAN	4015573185111
order unit	50 piece(s)

certificates / approvals

technical data

general

modular spacing	5 mm
soldering process	wave soldering
packaging	carton
number of poles	4
number of levels	1
marking	no
fastening	none
mating direction towards (circuit) board	90°

technical data

rated current	12 A
overvoltage category I	1000 V
overvoltage category II	400 V
overvoltage category III	250 V
rated impulse voltage	4 kV

technical data UL/CSA

voltage UL	300 V
current field wiring	15 A
current factory wiring	15 A
voltage CSA	300 V
current CSA	15 A

other


type of insulation material	thermoplastic
color	grey


height	12 mm
length	21.4 mm
depth	8.4 mm
material contact base	CuZn
material contact surface	Sn

assembly

item no.	type	description
25.220.3453.0	PCB connector 8113 B / 4 TOP OB	PCB female connector with front/top screw connection, 4 poles, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.220.0453.0	PCB connector 8113 B / 4 TOP	PCB female connector with front/top screw connection, 4 poles, printed version, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
01.060.3453.0	PCB connector 8113 BK / 4 OB	PCB female connector with Crimp connection, 4 poles, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
01.060.0453.0	PCB connector 8113 BK / 4	PCB female connector with Crimp connection, 4 poles, printed version, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color:grey
25.320.3453.0	PCB connector 8113 B / 4 OB	PCB female connector with screw connection with rising cage clamp system, 4 poles, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.320.0453.0	PCB connector 8113 B / 4	PCB female connector with screw connection with rising cage clamp system, 4 poles, printed version, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.325.3453.0	PCB connector 8113 B / 4 VR OB	PCB female connector with screw connection with rising cage clamp system, 4 poles, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.325.0453.0	PCB connector 8113 B / 4 VR	PCB female connector with screw connection with rising cage clamp system, 4 poles, printed version, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.326.3453.0	PCB connector 8113 B / 4 VL OB	PCB female connector with screw connection with rising cage clamp system, 4 poles, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.326.0453.0	PCB connector 8113 B / 4 VL	PCB female connector with screw connection with rising cage clamp system, 4 poles, printed version, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.820.3453.0	PCB connector 8113 BFK / 4 TOP OB	PCB female connector with tension spring connection, 4 poles, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey
25.820.0453.0	PCB connector 8113 BFK / 4 TOP	PCB female connector with tension spring connection, 4 poles, printed version, max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey


technical drawing





Schnitt A-A
section A-A

gezeichnete Ausführung: 8-polig
drawn version 8 poles



Weitere Daten siehe Katalog
further data see catalog

Farbe/colour	.F
grau/grey	.0
schwarz/black	.1
grün/green	.7
orange	.9

ⓐ

Teile-Nr. part no.	Pol-zahl	L	l	Typ type	Teile-Nr. part no.	Pol-zahl	L	l	Typ type
25.330.3253.F	2	11,4	5	8113S/ 2G0B	25.330.4353.F	13	66,4	60	8113S/13G0B
25.330.3353.F	3	16,4	10	8113S/ 3G0B	25.330.4453.F	14	71,4	65	8113S/14G0B
25.330.3453.F	4	21,4	15	8113S/ 4G0B	25.330.4553.F	15	76,4	70	8113S/15G0B
25.330.3553.F	5	26,4	20	8113S/ 5G0B	25.330.4653.F	16	81,4	75	8113S/16G0B
25.330.3653.F	6	31,4	25	8113S/ 6G0B	25.330.4753.F	17	86,4	80	8113S/17G0B
25.330.3753.F	7	36,4	30	8113S/ 7G0B	25.330.4853.F	18	91,4	85	8113S/18G0B
25.330.3853.F	8	41,4	35	8113S/ 8G0B	25.330.4953.F	19	96,4	90	8113S/19G0B
25.330.3953.F	9	46,4	40	8113S/ 9G0B	25.330.5053.F	20	101,4	95	8113S/20G0B
25.330.4053.F	10	51,4	45	8113S/10G0B	25.330.5153.F	21	106,4	100	8113S/21G0B
25.330.4153.F	11	56,4	50	8113S/11G0B	25.330.5253.F	22	111,4	105	8113S/22G0B
25.330.4253.F	12	61,4	55	8113S/12G0B	25.330.5353.F	23	116,4	110	8113S/23G0B
					25.330.5453	24	121,4	115	8113S/24G0B

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale 2:1

Vol. mm³ Oft./Srf. mm²

	Tag/Date	Name
gezeichnet drawn	14.10.2005	Schmitt J.
geprüft checked		
Normgepr. Stand. check		

Zeichnung Nr. / Drawing No.: T 25.330.3253.0 01K

Index: a

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
a	18.10.2019 /	

wieland
www.wieland-electric.com

Type: 8113 S / ..G 0B

Bennenung/Title: LP_GEHAEUSESTIFTLEISTE
Rastermaß 5 / pitch 5
PCB header

25_330_3253_0_01K-AA-dwg1_main_2 CADW4035 Lunz 2019-10-18T10:03:37 1.000

QU-MEE-01/14 a

These dimensions will be especially checked at delivery
Only inspection dimensions
With Ⓔ marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Ⓔ gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.