product data sheet

item no. 96.232.1034.1

cable assembly RST20I3K1-S 15 10SW

RST® CLASSIC connection cable, free end - male, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H07RN-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black



item no.	96.232.1034.1
EAN	4015573761902
order unit	50 piece(s)

certificates / approvals

technical data

note

note	The total length may vary up to + / - 3 %.

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	11.95 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
Pole codification	L, N, PE
color of housing inclusive strain relief	black

model

type of construction	shrinkage tube
connection type	crimp
nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP66/68 (3m;2h)
wire strip length	9 mm
sheath strip length	35 mm
preparation of conductor ends	ultrasonically compressed wire ends
cable type	H07RN-F
cable color	black
cable diameter min.	9.6 mm
cable diameter max.	10 mm
version of cable	male - free end

type of cord set	connection cable
version cable end 1	free end
version cable end 2	male
shielded	no


material


surface finish	silver-plated
halogen free	no
continuous temperature of cable	60 °C
insulation components continous temperature	100 °C
fire load	0.712 kWh/St
fire class	Eca

dimensions

total length	1 m

technical drawing





These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung bleiben vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Farbe/*colour*	
schwarz/*black*	.1
lichtgrau/*light grey*	.0
betongrau/*concrete grey*	.3

Teile-Nr. *part - no.*	L	Beispiel (Farbe: schwarz, lichtgrau) *exampel (colour: black, light grey)*	Typ *type*
96.232.XX34.1	XX in dm-Schritten	96.232.1034.1 = 10dm/L= 1000mm	RST2013K1-S 15 10SW
96.232.XX34.0		96.232.1034.0	RST2013K1-S 15 10GL
U6.232.XX34.1	XX in m-Schritten	U6.232.1234.1 = 12 m/L=12000mm	RST2013K1-S 15 X12SW
U6.232.XX34.0		U6.232.1234.0	RST2013K1-S 15 X12GL

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Weitere Daten siehe Katalog
further data see catalog

/		Werkstoff/Material	2007	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
/			gezeichnet drawn	22.02.	Kneitz	T 96.232.0434.0 01K	a
/		Maßstab/Scale	geprüft checked	-	-		
/		%	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
/		Vol. mm³	Ofl./Surf. mm²	Ersatz für/Replacement for: -			
/							
a	15.10.2014/	wieland www.wieland-electric.com		Type	Benennung/Title	KONFEKT_LEITUNG	
Index	Datum / Blatt Date / Sheet					freies Ende-Stecker Crimpausführun/free-end-male pre-assembled cable crimp design K1 250V	
Änderung/Revision							