product data sheet

item no. 96.030.0151.4

distributor RST20I3V 3P1 F V L BR0

RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 3, rated voltage 50 V / 120 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier signal brown



item no.	96.030.0151.4
EAN	4015573965638
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
marking of poles	1, 2, PE
RAL-number coding/insert connector	8002

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	distribution block

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.23 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	55.5 mm
width	85.8 mm
height	31.3 mm


accessories

item no.	type	description

05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black


technical drawing

Gezeichnete Ausführung: 96.030.0151.4
drawn construction:96.030.0151.4




Verpackungseinheit: je 100 Stück
packaging unit: per 100

Ausführung:96.030.0251.4
Variante: ohne Anschraubflansch
M1:1
drawn construction: 96.030.0251.4
variante: without screwing flange
M1:1



Type:RST20I3V 3P1 V L BR01

Ausführung:96.030.0151.4
Variante: mit Anschraubflansch
M1:1
drawn construction: 96.030.0151.4
variante: with screwing flange
M1:1



Type:RST20I3V 3P1 F V L BR01

Toleranz nach DIN 7167/Tolerance system acc. to DIN 7167. (This DIN-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).					ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TDM-05/03 ist einzuhalten. Conformity with Wieland document UU-TDM-05/03 (list of prohibited / declarable hazardous substances) to be declared!		
Freitoleranz nach General Tolerance		CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed			1.Verwendung: First Use: -	Blatt: Sheet: 1 von of 1	
/		Werkstoff/Material	2007	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
/			gezeichnet/drawn	02.04.	Kneitz	96.030.0151.4 01K	b
/	Maßstab/Scale 2:1	Farbe: signalbraun, ähnl. RAL 8002	geprüft/checked	-	-		
/			Normgep./Stand. check	-	-	Maße in mm/Dimensions are in mm	
/	Vol. mm³	Oll./Surf. mm²	Ersatz für/Replacement for: -				
b	30.04.2009/	wieland Elektrische Verbindungen	Type		Benennung/Title VERTEILER 3-polig für 50V		
a	18.01.2008/						
Index	Datum / Blatt Date / Sheet						
Änderung/Revision							QU-PEM-08/91

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.