
product data sheet

item no. 96.020.0150.8

distributor RST20I2V 3P1 F V L KG0

RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 2, rated voltage 50 V / 120 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier pebble grey



item no.	96.020.0150.8
EAN	4015573959064
order unit	100 piece(s)

certificates / approvals

RINA

technical data

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pebble grey
marking of poles	+, -
RAL-number coding/insert connector	7032

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	distribution block

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.227 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions


length	55.5 mm
width	85.8 mm
height	31.3 mm

accessories


item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black

technical drawing

Gezeichnete Ausführung:
drawn construction:
96.020.0150.8




Ausführung: 96.020.0250.8
Variante: ohne Anschraubflansch
drawn construction: 96.020.0250.8
variante: without screwing flange
M1:1



Typ/type: RST2012V 3P1 V L KG06

Ausführung: 96.020.0150.8
Variante: mit Anschraubflansch
drawn construction: 96.020.0150.8
variante: with screwing flange
M1:1



Typ/type: RST2012V 3P1 F V L KG06

Toleranz nach DIN 7167/Tolerance system acc. to DIN 7167. (This DIN-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).						ja/yes ☒ Stoffverbots- und Deklarationsliste nach WI-TDM-05/03 ist einzuhalten. Conformity with Wieland document WI-TDM-05/03 (list of prohibited / declarable hazardous substances) to be declared!	
Freitoleranz nach General Tolerance				CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed		1.Verwendung: First Use: -	Blatt: Sheet: 1 von of 1
/		Werkstoff/Material		2007	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
/		Farbe: kieselgrau, ähnl. RAL 7032 color: pebble grey, similar to RAL 7032		gezeichnet/drawn	13.02.	Winkler	T 96.020.0150.8 01K	b
/	Maßstab/Scale 2:1			geprüft/checked	-	-		
/				Normgep./Stand. check	-	-	Maße in mm/Dimensions are in mm	
/	Vol. mm³	Oll./Surf. mm²		Ersatz für/Replacement for: -				
b	30.04.2009/	wieland Elektrische Verbindungen		Type		Benennung/Title VERTEILER für AS-Interface/ for AS-Interface		
a	26.03.2007/							
Index	Datum / Blatt Date / Sheet							
Änderung/Revision								

QU-PEM-08/91

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.