
Product data sheet

Item No. 96.222.2098.4

Cable assembly RST20I2K1-S315OL 20BR0

RST20i3/2 connection cable male - free end, 2 pole, assembled with shrinkage tube, application ~50V/-120V, 16A, cable type Ölflex classic 100, length 2.0m, cross section 1.5mm², coding color signal brown



Item No.	96.222.2098.4
EAN	4015573965928
Order Unit	50 Piece(s)

Certificates / Approvals

Technical data

Note

Note	The total length may vary up to + / - 3 %.

General

Rated current	16 A
Rated voltage	50 V / 120 V
Rated impulse voltage	4 kV
Pollution degree	3
Lockable	self-locking (unlocking by tool)
Color of coding/ contact carrier	signal brown
Marking of poles	1, 2
Color of housing inclusive strain relief	black

Model

type of construction	Shrinkage tube
Connection type	Crimp
Nominal cross section conductor	1.5 mm²
Degree of protection (IP)	IP66/68 (3m;2h)
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	ultrasonically compressed wire ends
Cable type	Ölflex® Classic 110
Cable color	Grey
Cable diameter min.	6 mm
Cable diameter max.	6.6 mm
Version of cable	male - free end

Type of cord set	connection cable
Version cable end 1	free end
Version cable end 2	male
Shielded	No


Material


Surface finish	Silver-plated
halogen free	No
Continuous temperature of cable	70 °C
Insulation components continous temperature	100 °C
Fire load	0 kWh

Dimensions

Total length	2 m

Technical drawing





Teile-Nr. part-no.	L	Beispiel (Farbe: signalbraun) exampel (colour: signalbrown)	Typ type
96.222.XX98.4	XX in dm-Schritten	96.222.1098.4 = 10dm/L= 1000mm	RST2012K1-S315OL 10BR01
U6.222.XX98.4	XX in m-Schritten	U6.222.1298.4 = 12 m/L=12000mm	RST2012K1-S315OLX12BR01

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material

Maßstab/Scale %

	Tag/Date	Name
2007		
gezeichnet drawn	29.03.	Kneitz
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No. T 96.222.0498.4 01K Index b

Maße in mm/Dimensions are in mm

Vol. mm³ Ofl./Surf. mm²

Ersatz für/Replacement for: 96.222.0488.0 01K von 19.03.2007 a

Index	Datum / Blatt Date / Sheet
b	08.05.2014/
a	29.03.2007/

Änderung/Revision

wieland
www.wieland-electric.com

Type

Benennung/Title

KONFEKT_LEITUNG

freies Ende-Stecker Crimpausführung/free end-male pre-assembled cable crimp design K1 50V

QU-MEE-01/14 -

96222049840 1K_□ CADW3027 Dversch 2014-05-08T14:34:26 1.000

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung vorbehalten.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig