product data sheet

item no. 96.223.1092.4

cable assembly RST20I2K1BS325OL 10BR0

RST® CLASSIC connecting cable, female - male, number of poles 2, rated voltage 50 V / 120 V, rated current 20 A, cable type Ölflex® Classic 110, total length 1 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier signal brown

item no.	96.223.1092.4
EAN	4015573965997
order unit	50 piece(s)

certificates / approvals

technical data

note

note	The total length may vary up to + / - 3 %.

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	7.94 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
Pole codification	1, 2
color of housing inclusive strain relief	black

model

type of construction	shrinkage tube
connection type	crimp
nominal cross section conductor	2.5 mm²
degree of protection (IP)	IP66/68 (3m;2h)
cable type	Ölflex® Classic 110
cable color	grey
cable diameter min.	8.5 mm
cable diameter max.	9.4 mm
version of cable	female - male
type of cord set	connecting cable
version cable end 1	female

version cable end 2	male
shielded	no

material

surface finish	silver-plated
halogen free	no
continuous temperature of cable	70 °C
insulation components continous temperature	100 °C
fire load	0.638 kWh/St

dimensions

total length	1 m

technical drawing



Teile-Nr. part-no.	L	Beispiel (Farbe: signalbraun) exampel (colour: signalbrown)	Typ type
96.223.XX92.4	XX in dm-Schritten	96.223.1092.4 = 10dm/L= 1000mm	RST2012K1BS3250L 10BR01
U6.223.XX92.4	XX in m-Schritten	U6.223.1292.4 = 12 m/L=12000mm	RST2012K1BS3250LX12BR01

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

Toleranz Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung:
First Use: -

Blatt: 1 von 1
Sheet: 1 of 1

Index	Datum / Blatt Date / Sheet	Änderung/Revision
c	26.05.2015/	
b	01.02.2008/	
a	30.03.2007/	

Werkstoff/Material

Maßstab/Scale: %

Vol. mm³ Ofl./Surf. mm²

	Tag/Date	Name
2007 gezeichnet drawn	30.03.	Kneitz
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 96.223.0492.4 01K Index c

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: 96.223.0482.4 01K von 19.03.2007 (a)

wieland
www.wieland-electric.com

Type

Benennung/Title

KONFEKT_LEITUNG

Buchse-Stecker Crimpausführung/female-male
pre-assembled cable crimp design K1 50V

©Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten. Copying as well as the communication of its contents to others without express authorization is prohibited.