product data sheet

item no. 96.222.5032.4

cable assembly RST20I2K1BS315 L 50BR0

RST® CLASSIC connecting cable, female - male, number of poles 2, rated voltage 50 V / 120 V, rated current 16 A, cable type H07RN-F, total length 5 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier signal brown



item no.	96.222.5032.4
EAN	4015573945920
order unit	15 piece(s)

certificates / approvals

technical data

note

note	The total length may vary up to + / - 3 %.

general

rated current	16 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	58.1 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
Pole codification	1, 2
color of housing inclusive strain relief	black

model

type of construction	shrinkage tube
connection type	crimp
nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP66/68 (3m;2h)
cable type	H07RN-F
cable color	black
cable diameter min.	8.5 mm
cable diameter max.	9.7 mm
version of cable	female - male
type of cord set	connecting cable
version cable end 1	female
version cable end 2	male

shielded	no


material

surface finish	silver-plated
halogen free	no
continuous temperature of cable	60 °C
insulation components continous temperature	100 °C
fire load	3.223 kWh/St

dimensions

total length	5 m

technical drawing



Teile-Nr. part-no.	L	Beispiel exampel	Typ type
96.222.XX32.4	XX in dm-Schritten	96.222.1032.4 = 10dm/L= 1000mm	RST2012K1BS315 L 10SW
U6.222.XX32.4	XX in m-Schritten	U6.222.1232.4 = 12 m/L=12000mm	RST2012K1BS315 LX12SW

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material

Maßstab/Scale %

Vol. mm³ Oft./Surf. mm²

	Tag/Date	Name
2013		
gezeichnet drawn	03.07.	Schmitt J.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No. 96.222.0432.4 01K Index a

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: Zchng gl. Nr. vom 14.11.06 (a)

Index	Datum / Blatt Date / Sheet
a	03.07.2013/

Änderung/Revision

wieland
Elektrische Verbindungen

Type

Benennung/Title

KONFEKT_LEITUNG

Buchse-Stecker Crimpausführung / female-male pre-assembled cable crimp design K1 50V

96222043240 1K_2 CADW3029 Schmitt 2013-07-04 DE 13:26 1.000

OU-PEM-08/91b

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. All rights reserved. Any copying or reproduction of this document as well as the communication of its contents to others without express authorization is prohibited.