product data sheet

item no. 96.021.4251.4

connector RST20I2S B13ZRXS L BR0

RST® CLASSIC connector, splitter connector, number of poles 2, female, connection type screw connection, rated voltage 50 V / 120 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier signal brown



item no.	96.021.4251.4
EAN	4015573907638
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
Pole codification	1, 2
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	8002

connection data

cable diameter max.	10 mm
cable diameter min.	6 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	42 mm
wire strip length	8 mm

model

model	female
connection type	screw connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.513 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	97 mm
width	59 mm
height	38 mm


accessories


item no.	type	description
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black

assembly


item no.	type	description
96.020.0151.4	distributor RST20I2V 3P1 F V L BR0	RST® CLASSIC distribution block 1I / 3O, rated voltage 50 V / 120 V, rated current 20 A, number of poles 2, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 3, pole codification 1, 2, color of coding/ contact carrier signal brown, ral number coding/contact inse

technical drawing






Auslieferungszustand
delivery status



Verpackungseinheit: je 100 Stück
packaging unit: per 100

A-A





Type: RST2012S B13ZRXS L BR01

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material	2006	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
	gezeichnet / drawn	20.04.	Kneitz	96.021.4251.4 01K	
Maßstab/Scale 1:1	geprüft / checked	-	-		
	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
Vol. mm³	Oll./Surf. mm²	Ersatz für/Replacement for: -			

wieland — Elektrische Verbindungen

Type

Benennung/Title

BUCHSENTEIL_M_DOPPELZUGENTL
female connector with double cord grip
Schraubanschluss ohne Drahtschutz/screw-connection without wire protection
Kodierung/keying 1 (50V/20A)

Index | Datum / Blatt / Date / Sheet | Änderung/Revision

960214251401K CADW1019 Kneitz 2006-04-20T13:10:21 0.976

QU-PEM-08/91

960214251401K_2 CADW1005 Kuethe 2006-04-20T15:48:31 1.000

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of the contents to others without express authorization is prohibited.