product data sheet

item no. 92.934.0053.0

connector GST18I3F S2 ZR1 WS

gesis® CLASSIC connector, number of poles 3, male, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 7.8 - 10.3 mm, color of coding/ contact carrier white



item no.	92.934.0053.0
EAN	4015573402553
order unit	50 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	L, N, PE
color of housing inclusive strain relief	white
RAL-Nummer Codierung/Kontakteinsatz	9016

connection data

cable diameter max.	10.3 mm
cable diameter min.	7.8 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.5 mm²
connection cross section fine stranded mm² max.	1.5 mm²
connection cross section fine stranded mm² min.	0.5 mm²
terminations per pole	2
sheath strip length	45 mm
wire strip length	9 mm

model

model	male
connection type	spring clamp connection
degree of protection (IP)	IP40
remark to type of connection	fine- and multi stranded wires require a ferrule or a ultra sonically compacting

material

housing material	polyamide

halogen free	yes
contact material	CuZn
fire load	0.121 kWh/St
insulation components continous temperature	100 °C
surface finish	tin-plated

dimensions

length	75 mm
width	32.5 mm
height	15.5 mm

accessories

item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
06.561.7853.0	mounting frame GST18I3 SW	Mounting frame to snap in GST18i3 connectors into a housing or furniture. Wall thickness: 1,5-2,5 mm. Holds GST18i3 connectors with screw or spring connection and pre- assembled cables.
05.561.3653.0	cover cap GST18I3VS B WS	Cover piece for female GST18i3, white
05.561.3653.1	cover cap GST18I3VS B SW	Cover piece for female GST18i3, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.594.4250.0	cover cap ST18/3B + GST18I3 ST WS	
05.594.4253.0	cover cap ST18/3B + GST18I3 ST WS	


assembly

item no.	type	description
92.933.0053.0	connector GST18I3F B2 ZR1 WS	gesis® CLASSIC connector, number of poles 3, female, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 7.8 - 10.3 mm, color of coding/ contact carrier white
92.033.0058.0	device connector GST18I3L B1H WS	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier white
92.232.1007.2	cable assembly GST18I3K1BD 15 10WS	gesis® CLASSIC mains connection cable, female - power plug, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier white
92.033.0158.0	device connector GST18I3L B1H GR01	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier pebble grey
92.033.0658.0	device connector GST18I3L B1H BR05	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier brown
92.232.1000.2	cable assembly GST18I3K1BS 15 10WS	gesis® CLASSIC connecting cable, female - male, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier white
92.232.1003.2	cable assembly GST18I3K1B- 15 10WS	gesis® CLASSIC connection cable, female - free end, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier white
92.232.1004.2	cable assembly GST18I3K1-S 15 10WS	gesis® CLASSIC connection cable, male - free end, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier white
92.297.1003.0	cable assembly GST18I3KSB- 15 10TR01	gesis® CLASSIC connection cable, female - free end, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier tomato red
92.033.0758.0	device connector GST18I3L B1H RT03	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier salmon pink
92.033.0858.0	device connector GST18I3L B1H H RT03	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier salmon pink
92.033.0358.0	device connector GST18I3L B1H GN07	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier may green
92.033.0558.0	device connector GST18I3L B1H TB06	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue


92.033.0458.0	device connector GST18I3L B1H PB04	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier pastel blue


technical drawing

Auslieferungszustand: unmontiert
/delivery condition: unmounted



montierter Zustand
/mounted state





Teilenummer /part number	Farbe /colour	Typ /type
92.934.0053.0	weiß ähnl. RAL 9003 /white sim. RAL 9003	GST18I3F S2 ZR1 WS
92.994.0053.1	schwarz ähnl. RAL 9005 /black sim. RAL 9005	GST18I3F S2 ZR1 SW

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG
www.wieland-electric.com
eshop.wieland-electric.com

Toleranzierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (List of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material
Farbe /colour:
siehe Tabelle
/see table

Maßstab / Scale
2:1

Vol. mm³ Gfl./Srf. mm²

gezeichnet (drawn) Tag/Date 06.11.2025 Name Gähl M.

Elektronische Freigabe
Electronic Release

Ersatz für / Replacement for:

Zeichnung Nr. / Drawing No.
T 92.934.0053.0 13K
Index -

Maße in mm / Dimensions are in mm

Type

Benennung/Title
STECKERTEIL+ZE
/male connector with strain relief
250V AC 20A 2,5mm²

wieland

Index | Datum / Blatt
Date / Sheet
Änderung / Revision

2025-11-10 09:51:51 1.000

01-QU-RD-32/21

© Alle Rechte vorbehalten / All rights reserved
Vertraulichkeitsklasse / Confidentiality Class: Vertraulich / Confidential

These dimensions will be promptly checked at delivery
Only inserted dimensions are also valid for ordering use.
Dim. in express dimensions are also valid for ordering use.

Diese Maße werden bei Abnahme besonders geprüft
Nur eingetragene Maße sind auch für Bestellzwecke gültig.
Alle in express dimensions Maße sind auch für Bestellzwecke gültig.