product data sheet

item no. 96.022.0153.1

connector RST20I2F S23ZR2 V SW

RST® CLASSIC connector, straight, number of poles 2, male, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black



item no.	96.022.0153.1
EAN	4015573904330
order unit	100 piece(s)

certificates / approvals

technical data

note

note	fine stranded and stranded conductors require cable end sleeve

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
marking of poles	L, N
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	9005

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.5 mm²
connection cross section fine stranded mm² max.	1.5 mm²
connection cross section fine stranded mm² min.	0.5 mm²
terminations per pole	2
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	1.5 mm²
sheath strip length	35 mm
wire strip length	14.5 mm

model

model	male
connection type	spring clamp connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.272 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	79.1 mm
width	34.6 mm
height	34.6 mm


accessories


item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
06.502.4300.0	screwdriver DIN 5264 A 0,4 X 2,5	Screw driver according to DIN 5264 A, blade: 0.4x2.5 mm, long and straight version
95.101.1300.0	ferrule crimping tool 0,08 - 10 mm²	Crimping tool for ferrules, wire strip length: 7-28 mm, nominal cross section: 0,08-10 mm², length of tool: 180 mm
06.600.3627.0	ferrule DIN 46228-E1-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.0 mm²/AWG17
06.600.3727.0	ferrule DIN 46228-E0,75-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.75-1.0 mm²/AWG17
06.600.3827.0	ferrule DIN 46228-E0,5-10	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.5 mm²/AWG20
06.600.3927.0	ferrule DIN 46228-E1,5-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.5 mm²/AWG16

assembly


item no.	type	description
96.020.0153.1	distributor RST20I2V 3P1 F V SW	RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 2, rated voltage 250 V, rated current 10 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black
96.021.0153.1	connector RST20I2F B23ZR2 SW	RST® CLASSIC connector, straight, number of poles 2, female, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black

technical drawing







Auslieferungszustand
delivery status



Verpackungseinheit: je 100 Stück

A-A





Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Teile-Nr./ part-nr.	Farbe:/ color:	Type	
96.022.0153.1	schwarz, ähnl. RAL 9005/ black, similar to RAL 9005	RST2012F S2 ZR2	SW
96.022.0153.0	lichtgrau, ähnl.RAL 7035/ lightgrey, similar to RAL 7035	RST2012F S2 ZR2	GL

Toleranzierung nach DIN 7167/Tolerance system acc. to DIN 7167. [This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances].

ja/yes ☒ Stoffverbots- und Deklarationsliste nach QU-TGM-05/03 ist einzuhalten. Conformity with Wieland document QU-TGM-05/03 [list of prohibited / declarable hazardous substances] to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: 1 von 1 Sheet: 1 of 1

Werkstoff/Material

Maßstab/Scale 1:1

Vol. mm³ Oft./Surf. mm²

2006 Tag/Date Name

gezeichnet drawn 03.06. Kneitz

geprüft checked - -

Normgerr Stand. check - -

Zeichnung Nr./Drawing No. T 96.022.0153.0 01K Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Type

Benennung/Title

STECKERTEIL_MIT_ZUGENTLASTUNG

male connector with cord grip

mit Federkraftanschluss/ with spring-clamp connection

wieland Elektrische Verbindungen

Index Datum / Blatt Date / Sheet Änderung/Revision

QU-PEM-08/91

9602201530O1K_4 G4QW1019 Kneitz 2006-04-03T11:26:18 1.000