product data sheet

item no. 72.300.1653.0

# female insert BAS BUS 16 2,5 69

Female insert revos basic, 16-poles, rated current: 16A, rated voltage:690V, with tin-plated contacts



| | |
|---|---|
| item no. | 72.300.1653.0 |
| EAN | 4015573227071 |
| order unit | 10 piece(s) |

## certificates / approvals

## technical data

**general**

| | |
|---|---|
| model | female insert |
| inflammability class of insulation material acc. with UL94 | V0 |
| color | grey |
| mating cycles | 200 |
| pollution degree | 3 |
| suitable for modular version | no |
| operating temperature range min. | -40 °C |
| operating temperature range max. | 120 °C |

**connection data**

| | |
|---|---|
| connection type | screw connection |
| number of poles | 14 |
| plus switching contacts | 2 |
| number of pole for rated current 2 | 0 |
| number of pole for rated current 3 | 0 |
| total number of poles (without ground contact) | 16 |
| with wire protection | yes |
| min. conductor diameter rigid (solid/stranded) | 0.5 mm² |
| max. conductor diameter rigid (solid/stranded) | 2.5 mm² |
| protective contact | yes |

**technical data UL/CSA**

| | |
|---|---|
| nominal voltage according to UL/CSA | 600 V |
| nominal current according UL | 16 A |
| nominal current according CSA | 16 A |
| min. conductor cross section flexible wire | 0.5 mm² |
| max. conductor cross section flexible wire | 2.5 mm² |
| conductor cross section flexible AWG wire | 22-12 AWG |

**model**

| | |
|---|---|
| with housing | no |

**contacts**

| | |
|---|---|
| contact material | copper alloy |
| surface | tin-plated |
| contact resistance | # 1.5 mOhm |
| wire strip length | 7 mm |

**screws head design/recomm. Torque**

| | |
|---|---|
| mounting screws | H1/0.5-0.7 Nm |
| clamping screws | H1/0.5-0.7 Nm |
| ground conductor screws | H2/1.2-1.6 Nm |

**technical data DIN EN 61984**

| | |
|---|---|
| nominal voltage | 690 V |
| nominal voltage face/ground | 690 V |
| nominal current | 16 A |
| rated impulse voltage | 8 kV |

## assembly

| item no. | type | description |
|---|---|---|
| 72.310.1653.0 | male insert BAS STS 16 2,5 69 | Male insert revos basic, 16-poles, rated current: 16A, rated voltage: 690V, with tin-plated contacts |
| 72.710.1658.0 | male insert BAS STC 16 69 | Male insert revos basic, 16-poles, rated current: 16A, rated voltage: 690V, with tin-plated contacts |
| 71.350.1635.0 | hood BAS GOT GG 16 M25 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the right side (IP54), low version, 16-poles |
| 71.350.1635.1 | hood BAS GOT GG 16 M25 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the right side, low version, 16-poles |
| 71.350.1635.2 | hood BAS GOT GG 16 M25 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the right side, low version, 16-poles |
| 71.350.1635.3 | hood BAS GOT GG 16 M25 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the right side (IP54), low version, 16-poles |
| 71.352.1635.0 | hood BAS GOT GI 16 M25 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the top (IP54), low version, 16-poles |
| 71.352.1635.1 | hood BAS GOT GI 16 M25 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the top, low version, 16-poles |
| 71.352.1635.2 | hood BAS GOT GI 16 M25 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the top, low version, 16-poles |
| 71.352.1635.3 | hood BAS GOT GI 16 M25 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the top (IP54), low version, 16-poles |
| 71.353.1635.0 | hood BAS GOT GG 16 M32 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the right side (IP54), low version, 16-poles |
| 71.353.1635.1 | hood BAS GOT GG 16 M32 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the right side, low version, 16-poles |
| 71.353.1635.2 | hood BAS GOT GG 16 M32 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the right side, low version, 16-poles |
| 71.353.1635.3 | hood BAS GOT GG 16 M32 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the right side (IP54), low version, 16-poles |
| 71.354.1635.0 | hood BAS GOT GI 16 M32 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the top (IP54), low version, 16-poles |
| 71.354.1635.1 | hood BAS GOT GI 16 M32 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the top, low version, 16-poles |
| 71.354.1635.2 | hood BAS GOT GI 16 M32 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the top, low version, 16-poles |
| 71.354.1635.3 | hood BAS GOT GI 16 M32 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the top (IP54), low version, 16-poles |
| 71.372.1635.0 | hood BAS GOT GL 16 M25 A0 | Hood revos basic made of aluminum, with single locking lever and cable gland M25 on the top - free cable connection (IP54), low version, 16-poles |
| 71.372.1635.1 | hood BAS GOT GL 16 M25 A1 | Hood revos basic made of aluminum, with single locking lever and threaded hole M25 on the top - free cable connection, low version, 16-poles |
| 71.372.1635.3 | hood BAS GOT GL 16 M25 A3 | Hood revos basic made of aluminum, with single locking lever and trumpet gland M25 on the top - free cable connection (IP54), low version, 16-poles |
| 71.450.1637.1 | hood BAS GOM GG16 M25 B1 | Hood revos basic metal-series without coating, for single locking lever with threaded hole M25 on the right side, low version, 16-poles |
| 71.452.1637.1 | hood BAS GOM GI16 M25 B1 | Hood revos basic metal-series without coating, for single locking lever with threaded hole M25 on the top, low version, 16-poles |

| | | |
|---|---|---|
| 71.472.1637.1 | hood BAS GOM GL16 M25 B1 | Hood revos basic metal-series without coating, with single locking lever and threaded hole B1 on the top - free cable connection, low version,M2-poles |
| 76.350.4035.0 | hood BAS GOT GG 40HM25 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the right side (IP54), low version, 40-poles |
| 76.350.4035.1 | hood BAS GOT GG 40HM25 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the right side, low version, 40-poles |
| 76.350.4035.2 | hood BAS GOT GG 40HM25 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the right side, low version, 40-poles |
| 76.350.4035.3 | hood BAS GOT GG 16H M25 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the right side (IP54), low version, 16-poles |
| 76.351.1635.0 | hood BAS GOT GH 10H M20 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M20 on the front (IP54), low version, 10-poles |
| 76.351.1635.1 | hood BAS GOT GH 16H M20 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M20 on the front, low version, 16-poles |
| 76.351.1635.2 | hood BAS GOT GH 10H M20 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM20 on the front, low version, 10-poles |
| 76.351.1635.3 | hood BAS GOT GH 10H M20 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M20 on the front (IP54), low version, 10-poles |
| 76.352.4035.0 | hood BAS GOT GI 40HM25 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M25 on the top (IP54), low version, 40-poles |
| 76.352.4035.1 | hood BAS GOT GI 16HM25 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M25 on the top, low version, 16-poles |
| 76.352.4035.2 | hood BAS GOT GI 40HM25 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM25 on the top, low version, 40-poles |
| 76.352.4035.3 | hood BAS GOT GI 16H M25 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M25 on the top (IP54), low version, 16-poles |
| 76.353.4035.0 | hood BAS GOT GG 40HM32 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the right side (IP54), high version, size 16H |
| 76.353.4035.1 | hood BAS GOT GG 16HM32 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the right side, low version, 16-poles |
| 76.353.4035.2 | hood BAS GOT GG 40HM32 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the right side, low version, 40-poles |
| 76.353.4035.3 | hood BAS GOT GG 16H M32 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the right side (IP54), low version, 16-poles |
| 76.354.4035.0 | hood BAS GOT GI 40HM32 50 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the top (IP54), low version, 40-poles |
| 76.354.4035.1 | hood BAS GOT GI 40HM32 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the top, low version, 40-poles |
| 76.354.4035.2 | hood BAS GOT GI 40HM32 50 A2 | Hood revos basic made of aluminum, for single locking lever with nozzleM32 on the top, low version, 40-poles |
| 76.354.4035.3 | hood BAS GOT GI 16H M32 A3 | Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the top (IP54), low version, 16-poles |
| 76.360.4035.0 | hood BAS GOT GG 16H M40 A0 | Hood revos basic made of aluminum, for single locking lever with cable gland M40 on the right side (IP54), low version, 16-poles |
| 76.360.4035.1 | hood BAS GOT GG 40HM40 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M40 on the right side, low version, 40-poles |
| 76.362.4035.1 | hood BAS GOT GI 40HM40 50 A1 | Hood revos basic made of aluminum, for single locking lever with threaded hole M40 on the top, low version, 40-poles |
| 76.374.4035.0 | hood BAS GOT GL 40HM32 50 A0 | Connectors for free cable connections revos basic made of aluminum, with single locking lever and cable gland M32 on the top - free cable connection (IP54), 40-poles |
| 71.320.1628.0 | bottom BAS GUT GK 16 A | Bottom-base revos basic made of aluminum, with single locking lever, open, low version, 16-poles |
| 71.325.1628.0 | bottom BAS GUT GP 16 A | Bottom-base revos basic made of aluminum, with single locking lever, open, low version, 16-poles |
| 71.330.1635.0 | bottom BAS GUT GL 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right and left side (IP54), low version, 16-polig |
| 71.330.1635.1 | bottom BAS GUT GL 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right and left side, low version, 16-polig |
| 71.331.1635.0 | bottom BAS GUT GM 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the left side (IP54), low version, 16-polig |
| 71.331.1635.1 | bottom BAS GUT GM 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the left side, low version, 16-polig |
| 71.333.1635.0 | bottom BAS GUT GO 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the bottom (IP54), low version, 16-polig |
| 71.333.1635.1 | bottom BAS GUT GO 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the bottom, low version, 16-polig |
| 71.340.1635.0 | bottom BAS GUT GR 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right and the left side, with protective cover (IP54), low version, 16-polig |

| | | |
|---|---|---|
| 71.340.1635.1 | bottom BAS GUT GR 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right and the left side, with protective cover, low version, 16-polig |
| 71.341.1635.0 | bottom BAS GUT GS 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the left side, with protective cover (IP54), low version, 16-polig |
| 71.341.1635.1 | bottom BAS GUT GS 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the left side, with protective cover, low version,16-polig |
| 71.342.1635.0 | bottom BAS GUT GT 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right side, with protective cover (IP54), low version, 16-polig |
| 71.342.1635.1 | bottom BAS GUT GT 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right side, with protective cover, low version, 16-polig |
| 71.343.1635.0 | bottom BAS GUT GU 16 M25 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the bottom, with protective cover (IP54), low version, 16-polig |
| 71.343.1635.1 | bottom BAS GUT GU 16 M25 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the bottom, with protective cover, low version, 16-polig |
| 71.420.1637.0 | bottom BAS GUM GK 16 B | Bottom-base revos basic metal-series without coating, open, low version, 16-poles |
| 71.425.1637.0 | bottom BAS GUM GP 16 B | Bottom-base revos basic metal-series without coating, with single locking lever and protective cover, low version, 16-poles |
| 71.430.1637.1 | bottom BAS GUM GL 16 M25 B1 | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the right and left side, low version, 16-polig |
| 71.431.1637.1 | bottom BAS GUM GM 16 M25 B1 | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the left side, low version, 16-polig |
| 71.440.1637.1 | bottom BAS GUM GR 16 M25 B1 | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the right and the left side, with protective cover, low version, 16-polig |
| 71.441.1637.1 | bottom BAS GUM GS 16 M25 B1 | Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the left side, with protective cover, low version, 16-polig |
| 76.330.4035.0 | bottom BAS GUT GL 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right and left side (IP54), low version, 40-polig |
| 76.330.4035.1 | bottom BAS GUT GL 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right and left side, low version, 40-polig |
| 76.331.4035.0 | bottom BAS GUT GM 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the left side (IP54), low version, 40-polig |
| 76.331.4035.1 | bottom BAS GUT GM 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the left side, low version, 40-polig |
| 76.333.4035.0 | bottom BAS GUT GO 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the bottom (IP54), low version, 40-polig |
| 76.333.4035.1 | bottom BAS GUT GO 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the bottom, low version, 40-polig |
| 76.334.4035.0 | bottom BAS GUT GL 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the right and left side (IP54), low version, 40-polig |
| 76.334.4035.1 | bottom BAS GUT GL 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the right and left side, low version, 40-polig |
| 76.335.4035.0 | bottom BAS GUT GM 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the left side (IP54), low version, 40-polig |
| 76.335.4035.1 | bottom BAS GUT GM 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the left side, low version, 40-polig |
| 76.337.4035.0 | bottom BAS GUT GO 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the bottom (IP54), low version, 40-polig |
| 76.337.4035.1 | bottom BAS GUT GO 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the bottom, low version, 40-polig |
| 76.340.4035.0 | bottom BAS GUT GR 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right and the left side, with protective cover (IP54), low version, 40-polig |
| 76.340.4035.1 | bottom BAS GUT GR 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right and the left side, with protective cover, low version, 40-polig |
| 76.341.4035.0 | bottom BAS GUT GS 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the left side, with protective cover (IP54), low version, 40-polig |
| 76.341.4035.1 | bottom BAS GUT GS 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the left side, with protective cover, low version,40-polig |
| 76.342.4035.0 | bottom BAS GUT GT 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right side, with protective cover (IP54), low version, 40-polig |
| 76.342.4035.1 | bottom BAS GUT GT 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right side, with protective cover, low version, 40-polig |
| 76.343.4035.0 | bottom BAS GUT GU 40HM25 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the bottom, with protective cover (IP54), low version, 40-polig |
| 76.343.4035.1 | bottom BAS GUT GU 40HM25 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the bottom, with protective cover, low version, 40-polig |
| 76.344.4035.0 | bottom BAS GUT GR 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the right and the left side, with protective cover (IP54), low version, 40-polig |
| 76.344.4035.1 | bottom BAS GUT GR 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the right and the left side, with protective cover, low version, 40-polig |

| | | |
|---|---|---|
| 76.345.4035.0 | bottom BAS GUT GS 16HM32 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the left side, with protective cover (IP54), low version, 16-polig |
| 76.345.4035.1 | bottom BAS GUT GS 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the left side, with protective cover, low version,40-polig |
| 76.346.4035.0 | bottom BAS GUT GT 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the right side, with protective cover (IP54), low version, 40-polig |
| 76.346.4035.1 | bottom BAS GUT GT 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the right side, with protective cover, low version, 40-polig |
| 76.347.4035.0 | bottom BAS GUT GU 40HM32 50 A0 | Bottom-base revos basic made of aluminum, with single locking lever andcable gland M32 on the bottom, with protective cover (IP54), low version, 40-polig |
| 76.347.4035.1 | bottom BAS GUT GU 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M32 on the bottom, with protective cover, low version, 40-polig |
| 70.350.1635.0 | hood BAS GOT GA 16 M25 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the right side (IP54), low version, 16-poles |
| 70.350.1635.1 | hood BAS GOT GA 16 M25 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the right side, low version, 16-poles |
| 70.350.1635.2 | hood BAS GOT GA 16 M25 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the right side, low version, 16-poles |
| 70.350.1635.3 | hood BAS GOT GA 16 M25 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the right side (IP54), low version, 16-poles |
| 70.352.1635.0 | hood BAS GOT GC 16 M25 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the top (IP54), low version, 16-poles |
| 70.352.1635.1 | hood BAS GOT GC 16 M25 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the top, low version, 16-poles |
| 70.352.1635.2 | hood BAS GOT GC 16 M25 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the top, low version, 16-poles |
| 70.352.1635.3 | hood BAS GOT GC 16 M25 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the top (IP54), low version, 16-poles |
| 70.353.1635.0 | hood BAS GOT GA 16 M32 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the right side (IP54), low version, 16-poles |
| 70.353.1635.1 | hood BAS GOT GA 16 M32 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the right side, low version, 16-poles |
| 70.353.1635.2 | hood BAS GOT GA 16 M32 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the right side, low version, 16-poles |
| 70.353.1635.3 | hood BAS GOT GA 16 M32 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M32 on the right side (IP54), low version, 16-poles |
| 70.354.1635.0 | hood BAS GOT GC 16 M32 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the top (IP54), low version, 16-poles |
| 70.354.1635.1 | hood BAS GOT GC 16 M32 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the top, low version, 16-poles |
| 70.354.1635.2 | hood BAS GOT GC 16 M32 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the top, low version, 16-poles |
| 70.354.1635.3 | hood BAS GOT GC 16 M32 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M32 on the top (IP54), low version, 16-poles |
| 70.355.1635.0 | hood BAS GOT GD 16 M25 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the right side (IP54), low version, 16-poles |
| 70.355.1635.1 | hood BAS GOT GD 16 M25 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the right side, low version, 16-poles |
| 70.355.1635.2 | hood BAS GOT GD 16 M25 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM25 on the right side, low version, 16-poles |
| 70.355.1635.3 | hood BAS GOT GD 16 M25 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the right side (IP54), low version, 16-poles |
| 70.357.1635.0 | hood BAS GOT GF 16 M25 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the top (IP54), low version, 16-poles |
| 70.357.1635.1 | hood BAS GOT GF 16 M25 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the top, low version, 16-poles |
| 70.357.1635.2 | hood BAS GOT GF 16 M25 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM25 on the top, low version, 16-poles |
| 70.357.1635.3 | hood BAS GOT GF 16 M25 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the top (IP54), low version, 16-poles |
| 70.358.1635.0 | hood BAS GOT GD 16 M32 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the right side (IP54), low version, 16-poles |
| 70.358.1635.1 | hood BAS GOT GD 16 M32 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the right side, low version, 16-poles |
| 70.358.1635.2 | hood BAS GOT GD 16 M32 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the right side, low version, 16-poles |
| 70.358.1635.3 | hood BAS GOT GD 16 M32 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the right side (IP54), low version, 16-poles |

| | | |
|---|---|---|
| 70.359.1635.0 | hood BAS GOT GF 16 M32 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the top (IP54), low version, 16-poles |
| 70.359.1635.1 | hood BAS GOT GF 16 M32 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the top, low version, 16-poles |
| 70.359.1635.2 | hood BAS GOT GF 16 M32 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the top, low version, 16-poles |
| 70.359.1635.3 | hood BAS GOT GF 16 M32 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the top (IP54), low version, 16-poles |
| 70.372.1635.0 | hood BAS GOT GK 16 M25 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the top - free cable connection (IP54), low version, 16-poles |
| 70.372.1635.1 | hood BAS GOT GK 16 M25 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the top - free cable connection, low version, 16-poles |
| 70.372.1635.3 | hood BAS GOT GK 16 M25 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the top - free cable connection (IP54), low version, 16-poles |
| 72.250.1635.2 | hood POW GOT GA 16 M40 69 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M40 on the right side, low version, 16-poles |
| 73.350.4035.0 | hood BAS GOT GA 16HM25 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the right side (IP54), low version, 16-poles |
| 73.350.4035.1 | hood BAS GOT GA 16HM25 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the right side, high version, 16-poles |
| 73.350.4035.2 | hood BAS GOT GA 16HM25 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the right side, low version, 16-poles |
| 73.350.4035.3 | hood BAS GOT GA 16H M25 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the right side (IP54), low version, 16-poles |
| 73.351.1635.0 | hood BAS GOT GB 16H M25 A0 | Hood revos basic made of aluminum, for double locking lever and cable gland M25 on the front (IP54), low version, 16-poles |
| 73.351.1635.1 | hood BAS GOT GB 16H M25 A1 | Hood revos basic made of aluminum, for double locking lever and threaded hole M25 on the front, low version, 16-poles |
| 73.351.1635.2 | hood BAS GOT GB 16H M25 A2 | Hood revos basic made of aluminum, for double locking lever and nozzle M25 on the front, low version, 16-poles |
| 73.351.1635.3 | hood BAS GOT GB 16H M25 A3 | Hood revos basic made of aluminum, for double locking lever and trumpetgland M25 on the front (IP54), low version, 16-poles |
| 73.352.4035.0 | hood BAS GOT GC 16HM25 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M25 on the top (IP54), low version, 16-poles |
| 73.352.4035.1 | hood BAS GOT GC 16HM25 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M25 on the top, low version, 16-poles |
| 73.352.4035.2 | hood BAS GOT GC 16HM25 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M25 on the top, low version, 16-poles |
| 73.352.4035.3 | hood BAS GOT GC 16H M25 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M25 on the top (IP54), low version, 16-poles |
| 73.353.4035.0 | hood BAS GOT GA 40HM32 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the right side (IP54), high version, 40- poles |
| 73.353.4035.1 | hood BAS GOT GA 40HM32 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the right side, high version, 40-poles |
| 73.353.4035.2 | hood BAS GOT GA 40HM32 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the right side, low version, 40-poles |
| 73.353.4035.3 | hood BAS GOT GA 16HM32 A3 | Hood revos basic made of aluminum, for double locking lever or. screw cap with trumpet gland M32 on the right side (IP54), low version, 16-poles |
| 73.354.4035.0 | hood BAS GOT GC 16HM32 50 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the top (IP54), low version, 16-poles |
| 73.354.4035.1 | hood BAS GOT GC 16HM32 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the top, low version, 16-poles |
| 73.354.4035.2 | hood BAS GOT GC 16HM32 50 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the top, low version, 16-poles |
| 73.354.4035.3 | hood BAS GOT GC 16HM32 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M32 on the top, low version, 16-poles |
| 73.355.4035.0 | hood BAS GOT GD 16HM25 50 A0 | revos BASIC 500V size 16H hood with cable gland M25, lateral cable entry, with double locking levers, high design |
| 73.355.4035.1 | hood BAS GOT GD 16HM25 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the right side, low version, 16-poles |
| 73.355.4035.2 | hood BAS GOT GD 16HM25 50 A2 | revos BASIC 500V size 16H hood with intermediate support M25, lateral cable entry, with double locking levers, high design |
| 73.355.4035.3 | hood BAS GOT GD 16HM25 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM25 on the right side, low version, 16-poles |
| 73.357.4035.0 | hood BAS GOT GF 16HM25 50 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M25 on the top (IP54), low version, 16-poles |
| 73.357.4035.1 | hood BAS GOT GF 16HM25 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M25 on the top, low version, 16-poles |

| | | |
|---|---|---|
| 73.357.4035.2 | hood BAS GOT GF 16HM25 50 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM25 on the top, low version, 16-poles |
| 73.357.4035.3 | hood BAS GOT GF 16HM25 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M25 on the top (IP54), low version, 16-poles |
| 73.358.4035.0 | hood BAS GOT GD 16HM32 50 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the right side (IP54), low version, 16-poles |
| 73.358.4035.1 | hood BAS GOT GD 16HM32 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the right side, low version, 16-poles |
| 73.358.4035.2 | hood BAS GOT GD 16HM32 50 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the right side, low version, 16-poles |
| 73.358.4035.3 | hood BAS GOT GD 16HM32 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the right side (IP54), low version, 16-poles |
| 73.359.4035.0 | hood BAS GOT GF 16HM32 50 A0 | Hood revos basic made of aluminum, with double locking lever and cable gland M32 on the top (IP54), low version, 16-poles |
| 73.359.4035.1 | hood BAS GOT GF 16HM32 50 A1 | Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the top, high version, 16-poles |
| 73.359.4035.2 | hood BAS GOT GF 16HM32 50 A2 | Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the top, low version, 16-poles |
| 73.359.4035.3 | hood BAS GOT GF 16HM32 A3 | Hood revos basic made of aluminum, with double locking lever and trumpet gland M32 on the top (IP54), low version, 16-poles |
| 73.360.4035.0 | hood BAS GOT GA 16HM40 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M40 on the right side (IP54), low version, 16-poles |
| 73.360.4035.1 | hood BAS GOT GA 16HM40 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M40 on the right side, high version, 16-poles |
| 73.360.4035.2 | hood BAS GOT GA 16HM40 A2 | Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M40 on the right side, low version, 16-poles |
| 73.362.4035.0 | hood BAS GOT GC 16HM40 A0 | Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M40 on the top (IP54), low version, 16-poles |
| 73.362.4035.1 | hood BAS GOT GC 16HM40 50 A1 | Hood revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M40 on the top, low version, 16-poles |
| 70.320.1628.0 | bottom BAS GUT GA 16 A | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap, low version, 16-poles |
| 70.325.1628.0 | bottom BAS GUT GE 16 A | Bottom-base revos basic made of aluminum, for double locking lever and protective cover, open, low version, 16-poles |
| 70.330.1635.0 | bottom BAS GUT GB 16 M25 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right and left side (IP54), low version, 16-polig |
| 70.330.1635.1 | bottom BAS GUT GB 16 M25 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right and left side, low version, 16-polig |
| 70.331.1635.0 | bottom BAS GUT GC 16 M25 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the left side (IP54), low version, 16-polig |
| 70.331.1635.1 | bottom BAS GUT GC 16 M25 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the left side, low version, 16-polig |
| 70.333.1635.0 | bottom BAS GUT GD 16 M25 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right side (IP54), low version, 16-polig |
| 70.333.1635.1 | bottom BAS GUT GD 16 M25 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right side, low version, 16-polig |
| 70.340.1635.0 | bottom BAS GUT GF 16 M25 A0 | Bottom-base revos basic made of aluminum, for double locking lever withcable gland M25 on the left and right side, with protective cover (IP54), low version, 16-polig |
| 70.340.1635.1 | bottom BAS GUT GF 16 M25 A1 | Bottom-base revos basic made of aluminum, for double locking lever withthreaded hole M25 on the left and right side, with protective cover, low version, 16-polig |
| 70.341.1635.0 | bottom BAS GUT GG 16 M25 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the left side, with protective cover (IP54), low version, 16-polig |
| 70.341.1635.1 | bottom BAS GUT GG 16 M25 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the left side, with protective cover, low version,16-polig |
| 70.342.1635.0 | bottom BAS GUT GH 16 M25 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the right side, with protective cover (IP54), low version, 16-polig |
| 70.342.1635.1 | bottom BAS GUT GH 16 M25 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the right side, with protective cover, low version, 16-polig |
| 70.343.1635.0 | bottom BAS GUT GI 16 M25 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the bottom, with protective cover (IP54), low version, 16-polig |
| 70.343.1635.1 | bottom BAS GUT GI 16 M25 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the bottom, with protective cover, low version, 16-polig |
| 73.330.4035.0 | bottom BAS GUT GB 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right and left side (IP54), low version, 16-polig |
| 73.330.4035.1 | bottom BAS GUT GB 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right and left side, low version, 16-polig |
| 73.331.4035.0 | bottom BAS GUT GC 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the left side (IP54), low version, 16-polig |

| | | |
|---|---|---|
| 73.331.4035.1 | bottom BAS GUT GC 16M25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the left side, low version, 16-polig |
| 73.333.4035.0 | bottom BAS GUT GD 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M25 on the right side (IP54), low version, 16-polig |
| 73.333.4035.1 | bottom BAS GUT GD 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M25 on the right side, low version, 16-polig |
| 73.334.4035.0 | bottom BAS GUT GB 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M32 on the right and left side (IP54), low version, 16-polig |
| 73.334.4035.1 | bottom BAS GUT GB 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the right and left side, low version, 16-polig |
| 73.335.4035.0 | bottom BAS GUT GC 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M32 on the left side (IP54), high version, 6-poles |
| 73.335.4035.1 | bottom BAS GUT GC 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the left side, low version, 16-polig |
| 73.337.4035.0 | bottom BAS GUT GD 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M32 on the right side (IP54), low version, 16-polig |
| 73.337.4035.1 | bottom BAS GUT GD 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the right side, low version, 16-polig |
| 73.338.4035.1 | bottom BAS GUT GB 16H M40 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the right and left side, low version, 16-polig |
| 73.339.4035.0 | bottom BAS GUT GC 16H M40 A0 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with cable gland M40 on the left side (IP54), low version, 16-polig |
| 73.339.4035.1 | bottom BAS GUT GC 16H M40 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the left side, low version, 16-polig |
| 73.340.4035.0 | bottom BAS GUT GB 16H M40 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the right and left side, low version, 16-polig |
| 73.340.4035.1 | bottom BAS GUT GF 16HM25 50 A1 | Bottom-base revos basic made of aluminum, for double locking lever withthreaded hole M25 on the left and right side, with protective cover, low version, 16-polig |
| 73.341.4035.0 | bottom BAS GUT GC 16H M40 A1 | Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M40 on the left side, low version, 16-polig |
| 73.341.4035.1 | bottom BAS GUT GG 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the left side, with protective cover, low version,16-polig |
| 73.342.4035.0 | bottom BAS GUT GH 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the right side, with protective cover (IP54), low version, 16-polig |
| 73.342.4035.1 | bottom BAS GUT GH 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the right side, with protective cover, low version, 16-polig |
| 73.343.4035.0 | bottom BAS GUT GI 16HM25 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M25 on the bottom, with protective cover (IP54), low version, 16-polig |
| 73.343.4035.1 | bottom BAS GUT GI 16HM25 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M25 on the bottom, with protective cover, low version, 16-polig |
| 73.344.4035.0 | bottom BAS GUT GF 16HM32 50 A0 | Bottom-base revos basic made of aluminum, for double locking lever withcable gland M32 on the left and right side, with protective cover (IP54), low version, 16-polig |
| 73.344.4035.1 | bottom BAS GUT GF 16HM32 50 A1 | Bottom-base revos basic made of aluminum, for double locking lever withthreaded hole M32 on the left and right side, with protective cover, high version, 16-polig |
| 73.345.4035.0 | bottom BAS GUT GG 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M32 on the left side, with protective cover (IP54), low version, 16-polig |
| 73.345.4035.1 | bottom BAS GUT GG 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M32 on the left side, with protective cover, low version,16-polig |
| 73.346.4035.0 | bottom BAS GUT GH 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M32 on the right side, with protective cover (IP54), low version, 16-polig |
| 73.346.4035.1 | bottom BAS GUT GH 16HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M32 on the right side, with protective cover, low version, 16-polig |
| 73.347.4035.0 | bottom BAS GUT GI 16HM32 50 A0 | Bottom-base revos basic made of aluminum, with double locking lever andcable gland M32 on the bottom, with protective cover (IP54), low version, 16-polig |
| 73.347.4035.1 | bottom BAS GUT GI 40HM32 50 A1 | Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M32 on the bottom, with protective cover, low version, 40-polig |

technical drawing

