product data sheet

item no. 73.359.6435.1

# hood BAS GOT GF 24HM32 50 A1

Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the top, low version, 24-poles




| | |
|---|---|
| item no. | 73.359.6435.1 |
| EAN | 4015573663701 |
| order unit | 1 piece(s) |

## certificates / approvals

## technical data


**general**


| | |
|---|---|
| housing material | aluminum |
| color | grey |
| surface | with powder coating |
| degree of protection (IP) | other |
| UV resistant | yes |
| inflammability class of insulation material acc. with UL94 | other |
| operating temperature range min. | -40 °C |
| operating temperature range max. | 120 °C |


**model**

| | |
|---|---|
| construction | 24H |
| model of the housing | male |
| locking mechanism | double locking levers |
| cable entry | above |
| type of cable | thread |
| with cable screw gland | no |
| thread size M | 32 |
| thread size PG | |
| hinged lid | no |
| EMC-version | no |
| length | 120 mm |
| width | 57 mm |
| height | 76 mm |

technical drawing





Varianten/ Variants

.0 .2 .3 .4 .5



| | | | |
|---|---|---|---|
| 67 73.359 .6435.5 57 | BAS GOT GF 24H | M40 M32 M25 A5 | Kabelverschraubung(KV), IP65 /Cable gland(CG), IP65 | |
| 67 73.359 .6435.4 57 | BAS GOT GF 24H | M40 M32 M25 A4 | KV mit Zugentlastung, IP54 /CG with strain relief, IP54 | |
| 73.3 59 57 .6435.3 | BAS GOT GF 24H | M32 M25 A3 | KV mit Zugentlastung und Knickschutz, IP54 /CG with strain relief and bend support, IP54 | |
| 67 73.359 .6435.2 57 | BAS GOT GF 24H | M40 M32 M25 A2 | Zwischenstutzen /Bushing | |
| 67 73.359 .6435.1 57 | BAS GOT GF 24H | M40 M32 M25 A1 | Gewindebohrung /Thread hole | X |
| 67 73.359 .6435.0 57 | BAS GOT GF 24H | M40 M32 M25 A0 | Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54 | |
| Bestellnummer /Order number | Typ /Type | | Varianten /Variants | dar-gestellt /drawed |

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. / Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff / Material: Aluminium beschichtet / coated grau / grey

Maßstab / Scale: 1:1

gezeichnet / drawn: Tag/Date 21.04.2021, Name: Schmitt J.

Elektronische Freigabe / Electronic Release

Zeichnung Nr. / Drawing No.: T 73.357.6435.0 13K

Index: a

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

| Index | Datum / Blatt Date / Sheet | Änderung / Revision |
|---|---|---|
| a | 20.04.2021 / | |

wieland

Type: revos BASIC

Bennenung/Title: GEHAEUSEOBERTEIL

Baugröße 24H-Kabelabgang 1x M25/M32/M40 oben

Hood size 24H-cable outlet 1xM25/M32/M40 top

Diese Maße werden bei Abnahme besonders geprüft / These dimensions will be especially checked at delivery

Ausschließlich Prüfmaße / Only inspection dimensions

Mit IE gekennzeichnete Maße sind nur für interne Zwecke gültig / With IE marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.