product data sheet

item no. 71.353.2435.0

hood BAS GOT GG 24 M32 A0

Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the right side (IP54), low version, 24-poles



item no.	71.353.2435.0
EAN	4015573651685
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model


construction	24
model of the housing	male
locking mechanism	single locking lever
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	136 mm
width	43 mm
height	70 mm

technical drawing





Varianten/ Variants



$71.35^{3}_{0}.2435.5$	BAS GOT GG 24 M32 M25 A 5	Kabelverschraubung(KV), IP65 /Cable gland(CG), IP65	
$71.35^{3}_{0}.2435.4$	BAS GOT GG 24 M32 M25 A 4	KV mit Zugentlastung, IP54 /CG with strain relief, IP54	
$71.35^{3}_{0}.2435.3$	BAS GOT GG 24 M32 M25 A 3	KV mit Zugentlastung und Knickschutz, IP54 /CG with strain relief and bend support, IP54	
$71.35^{3}_{0}.2435.2$	BAS GOT GG 24 M32 M25 A 2	Zwischenstutzen /Bushing	
$71.35^{3}_{0}.2435.1$	BAS GOT GG 24 M32 M25 A 1	Gewindebohrung /Thread hole	X
$71.35^{3}_{0}.2435.0$	BAS GOT GG 24 M32 M25 A 0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material: Aluminium beschichtet/ coated grau/ grey

Maßstab/Scale: 1:2

Vol. mm³ Oft./Surf. mm²

	Name	Tag/Date
2013		
gezeichnet drawn	Treschan	17.09.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 71.350.2435.0 13K

Index:

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Änderung/Revision | Index | Datum / Blatt Date / Sheet

wieland
Elektrische Verbindungen

Type: revos BASIC

Benennung/Title: GEHAEUSEOBERTEIL
Baugröße 24-Kabelabgang seitlich-M25/M32
Hood size 24-cable outlet side-M25/M32

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

71350243501K_2 CADW3028 Treschan 2013-09-20T09:38:24 1:000

OU-PEM-08/91b