

## product data sheet

item no. 73.344.4035.0

### bottom BAS GUT GF 16HM32 50 A0

Bottom-base revos basic made of aluminum, for double locking lever with cable gland M32 on the left and right side, with protective cover (IP54), low version, 16-polig



|            |               |
|------------|---------------|
| item no.   | 73.344.4035.0 |
| EAN        | 4015573627789 |
| order unit | 1 piece(s)    |

## certificates / approvals


## technical data

### general

|                                                          |                     |
|----------------------------------------------------------|---------------------|
| housing material                                         | aluminum            |
| color                                                    | grey                |
| surface                                                  | with powder coating |
| degree of protection (IP)                                | IP54                |
| UV resistant                                             | yes                 |
| flammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                         | -40 °C              |
| operating temperature range max.                         | 120 °C              |

### model

|                        |                         |
|------------------------|-------------------------|
| construction           | 16H                     |
| model of the housing   | surface mounting (base) |
| locking mechanism      | double locking levers   |
| cable entry            | two-sided               |
| type of cable          | gland nut               |
| with cable screw gland | yes                     |
| thread size M          | 32                      |
| thread size PG         |                         |
| hinged lid             | yes                     |
| EMC-version            | no                      |
| length                 | 117 mm                  |
| width                  | 57 mm                   |
| height                 | 98 mm                   |



|                                                                                        |                                                 |                                                         |                            |
|----------------------------------------------------------------------------------------|-------------------------------------------------|---------------------------------------------------------|----------------------------|
| 73.34 <sup>4</sup> <sub>0</sub> .4035.1                                                | BAS GUT GF 16H <sup>M32</sup> <sub>M25</sub> A1 | Gewindebohrung<br>/Thread hole                          | X                          |
| 73.34 <sup>4</sup> <sub>0</sub> .4035.0                                                | BAS GUT GF 16H <sup>M32</sup> <sub>M25</sub> A0 | Kabelverschraubung(KV), IP54<br>/Cable gland(ICG), IP54 |                            |
| Bestellnummer<br>/Order number                                                         | Typ<br>/Type                                    | Varianten<br>/Variants                                  | der-<br>gestellt<br>/drawn |
| Weitere Daten siehe KATALOG oder eKatalog.<br>Additional data see CATALOG or eCatalog. |                                                 | www.wieland-electric.com<br>eshop.wieland-electric.com  |                            |

|                                                                                                                                                                                                                                          |  |                          |  |                                                                                                                                                                                                             |  |                                                                                 |  |                                 |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------|--|---------------------------------|--|
| Tolerierung Size ISO 14005(☑)/Tolerance system Size ISO 14005(☑)<br>(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances). |  |                          |  | ja/yes ☑ Stoffverbot/- und Deklarationsliste nach WH 5020.010 ist einzuhalten.<br>Conformity with Wieland document WH 5020.010 e (list of prohibited /<br>declaimable hazardous substances) to be declared! |  |                                                                                 |  |                                 |  |
| Freitoleranz nach<br>General tolerance                                                                                                                                                                                                   |  | DIN ISO 2768 - m         |  | CAD - Zeichnung, keine manuellen Änderungen<br>CAD - drawing, no manual modifications allowed                                                                                                               |  | 1. Verwendung: -<br>First Use:                                                  |  | Blatt: 1 von 1<br>Sheet: 1 of 1 |  |
| /                                                                                                                                                                                                                                        |  | Werkstoff/Material       |  | 2014                                                                                                                                                                                                        |  | Tag/Date                                                                        |  | Name                            |  |
| /                                                                                                                                                                                                                                        |  | Aluminium                |  | gezeichnet<br>drawn                                                                                                                                                                                         |  | 21.08.                                                                          |  | Ireschan                        |  |
| / Maßstab/Scale                                                                                                                                                                                                                          |  | beschichtet/ coated      |  | geprüft<br>checked                                                                                                                                                                                          |  | - -                                                                             |  | - -                             |  |
| / 1:2                                                                                                                                                                                                                                    |  | grau/ grey               |  | normer-<br>Stand, check                                                                                                                                                                                     |  | - -                                                                             |  | - -                             |  |
| Maße in mm/Dimensions are in mm                                                                                                                                                                                                          |  |                          |  |                                                                                                                                                                                                             |  |                                                                                 |  |                                 |  |
| / Vol.                                                                                                                                                                                                                                   |  | mm                       |  | Of L./Surf.                                                                                                                                                                                                 |  | mm                                                                              |  | Ersatz für/Replacement for: -   |  |
| /                                                                                                                                                                                                                                        |  |                          |  | Type                                                                                                                                                                                                        |  | Benennung/Title                                                                 |  |                                 |  |
| /                                                                                                                                                                                                                                        |  |                          |  | revos                                                                                                                                                                                                       |  | GEHÄUSEUNTERTEIL                                                                |  |                                 |  |
| /                                                                                                                                                                                                                                        |  |                          |  | BASIC                                                                                                                                                                                                       |  | Baugröße 16H-Kabelabgang 2x M25/M32<br>housing size 16H-cable outlet 2x M25/M32 |  |                                 |  |
| Index Datum / Blatt<br>Date / Sheet                                                                                                                                                                                                      |  | www.wieland-electric.com |  |                                                                                                                                                                                                             |  |                                                                                 |  |                                 |  |
| Änderung/Revision                                                                                                                                                                                                                        |  |                          |  |                                                                                                                                                                                                             |  |                                                                                 |  |                                 |  |