product data sheet

item no. 71.331.1635.0

bottom BAS GUT GM 16 M25 A0

Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the left side (IP54), low version, 16-polig



item no.	71.331.1635.0
EAN	4015573621824
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	117 mm
width	57 mm
height	57 mm

technical drawing






Varianten/Variants
.0



71.331.1635.1	BAS GUT GM 16 M25 A 1	Gewindebohrung /Thread hole	X
71.331.1635.0	BAS GUT GM 16 M25 A 0	Kabelverschraubung(KV), IP54 montiert /Cable gland(CG), IP54 assembled	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com



Bohrbild
/Cut out

Toleranzierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: -
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff/Material

Maßstab/Scale 1:2

Vol. mm³ Oft./Surf. mm²

	Name	Tag/Date
2013		
gezeichnet drawn	Treschan	26.06.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No. T 71.331.1635.0 13K

Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index | Datum / Blatt Date / Sheet

Änderung/Revision

wieland
Elektrische Verbindungen

Type revos BASIC

Benennung/Title

GEHAEUSEUNTERTEIL

Baugröße 16-Kabelabgang 1xM25 links
Housing size 16-cable outlet 1xM25 left

71331163501 3K_2 CADW3028 Treschan 2013-09-20 17:34:18 1:000

OU-PEM-08/91b