

product data sheet

item no. 76.344.1035.0

bottom BAS GUT GR 10HM32 50 A0

Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the right and the left side, with protective cover (IP54), low version, 10-polig



item no.	76.344.1035.0
EAN	4015573844308
order unit	1 piece(s)

certificates / approvals

technical data

general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model


construction	10
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	yes
EMC-version	no
length	97 mm
width	58 mm
height	72 mm

Ausführung .1
version .1

Gezeichnete Ausführung .0 / version .0




Gewinde M32
thread M32




Verschraubung M32
screw connection M32

Verschraubung M32
screw connection M32

ca. 8



ca. 74,4



weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-no.	Typ type
76.344.1035.0	BAS GUT GR 10HM32 50 A0
76.344.1035.1	BAS GUT GR 10HM32 50 A1

Freitoleranz nach -				CAD - Zeichnung, keine manuellen Änderungen				1. Verwendung: -				Bl.: 1 von 1	
	/	Maßstab	Werkstoff und Oberfläche:		2004	Tag	Name	T	Zeichnung Nr.				Index
	/	x			Entworfen	13.08.	Karz H.		76.344.1035.0 01K				
	/				Geprüft	-	-						
	/	Vol.	mm ³	Blf.	mm ³	Normgepr.	-	-	Ersatz für: -				
	/	 wieland				Benennung							
a	09.06.2005/					GEHAEUSEUNTERTEIL							
Buchstabe	Datum / Blatt					housing lower part							
Änderung		Elektrische Verbindungen				Größe/size 10 2x M32							

Weitergabe sowie Vervielfältigung dieser Dokumente, Vervielfältigung und Mitteilung
sonstigen Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.

76.344.1035.01K_4 CADW27.dwg 2005-06-10 10:45:10