product data sheet

item no. 76.341.1035.0

bottom BAS GUT GS 10HM25 50 A0

Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the left side, with protective cover (IP54), low version, 10-polig



item no.	76.341.1035.0
EAN	4015573844292
order unit	1 piece(s)

certificates / approvals

technical data

general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model


construction	10
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	yes
EMC-version	no
length	97 mm
width	58 mm
height	72 mm


technical drawing


Ausführung .1
version .1



Gezeichnete Ausführung .0/version .0







weitere Daten siehe Katalog
further data see catalog

Teile-Nr.	Typ
76.341.1035.0	BAS GUT GS 10HM25 50 A0
76.341.1035.0	BAS GUT GS 10HM25 50 A1

Freitoleranz nach -
CAD - Zeichnung, keine manuellen Änderungen
1.Verwendung: -
Bl.: 1 von 1

Maßstab	Werkstoff und Oberfläche:		Name	Zeichnung Nr.	Index
x		Entworfen 08.10. 2004	Duetsch T.	T 76.341.1035.0 01K	a
		Geprüft	-		
		Vol. mm³ Oft. mm² Normgepr.	-	Ersatz für: -	

a 09.06.2005/ Änderung
Buchstabe Datum / Blatt

wieland
Elektrische Verbindungen

Benennung
GEHAEUSEUNTERTEIL
housing lower part
Größe 10/size 10 1x M25 mit Deckel/with cap

76341035001K_4 CADM027 duetsch 2005-06-10T10:52:21 1:1.000

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Ø gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.