


product data sheet

item no. 73.334.0635.0

bottom BAS GUT GL 6HM32 69 A0

Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the right and left side (IP54), high version, 6-polig



item no.	73.334.0635.0
EAN	4015573843929
order unit	1 piece(s)

certificates / approvals

technical data

general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	6H
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	84 mm
width	58 mm
height	72.2 mm




Ausführung .1
version .1

Gewinde M32 (2x)
thread M32 (2x)



Gezeichnete Ausführung .0 / version .0

Verschraubung M32 (2x)
screw connection M32 (2x)



weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-nr.	Typ type
73.334.0635.0	BAS GUT GL 6HM32 69 A0
73.334.0635.1	BAS GUT GL 6HM32 69 A1

Freitoleranz nach -				CAD - Zeichnung, keine manuellen Änderungen				1. Verwendung: -		Bl.: 1 von 1		
		/	Maßstab	Werkstoff und Oberfläche:		2004	Tag	Name		T	Zeichnung Nr. 73.334.0635.0 01K	Index
		/	x			Entworfen	27.10.	Ditsch T.				
		/				Geprüft	-	-				
		/				Vol.	mm ³	Bl.	mm ³			
		/	 wieland		Benennung GEHAEUSEUNTERTEIL IL HOUSING LOWER PART Größe/size 6 2x M32							
		/										
		/										
Buchstabe		Datum / Blatt		Elektrische Verbindungen								
Änderung												

Weitergabe sowie Vervielfältigung dieser Zeichnung, Vervielfältigung und Mitteilung
sonstigen Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.