product data sheet

item no. 46.051.4150.4

connector RST16I5 S B1 ZT5S L BR

RST® MINI connector, straight, number of poles 5, female, connection type screw connection, rated voltage 50 V / 120 V, rated current 16 A, cable diameter 10 - 14.5 mm, color of coding/ contact carrier signal brown



item no.	46.051.4150.4
EAN	4049088255755
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	16 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	signal brown
Pole codification	1, 2, 3, 4, 5
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	8002

connection data

cable diameter max.	14.5 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.25 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	0.25 mm²
terminations per pole	1
sheath strip length	25 mm
wire strip length	8 mm

model

model	female
connection type	screw connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.194 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

width	27 mm
height	27 mm


accessories

item no.	type	description
06.563.9053.1	cover for female connector SW	RST16i5/4 cover piece, for covering unused female connectors, color black
06.563.9153.1	cover for female connector SW	RST16i5/4 cover piece, for covering unused female connectors, with fastening belt, color black


assembly

item no.	type	description
46.052.5050.4	device connector RST16I5 S S1 M03 L BR	RST® MINI device connector, standard, straight, M20.2, number of poles 5, model male, connection type screw connection, rated voltage 50 V / 120 V, rated current 16 A, color of coding/ contact carrier signal brown
46.050.1250.4	distributor RST16I5V 2P1 TGVGL BR	RST® MINI distribution block 1I / 2O, rated voltage 50 V / 120 V, rated current 16 A, number of poles 5, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 2, pole codification 1, 2, 3, 4, 5, color of coding/ contact carrier signal brown, ral number coding/ con
46.052.4150.4	connector RST16I5 S S1 ZT5S L BR BR	RST® MINI connector, straight, number of poles 5, male, connection type screw connection, rated voltage 50 V / 120 V, rated current 16 A, cable diameter 10 - 14.5 mm, color of coding/ contact carrier signal brown


technical drawing




Kodierung
/Coding



Auslieferungszustand/
delivery condition





46.051.4153.9	RST1615S B1 ZW4S H BL	C4	lichtblau /light blue
46.051.4150.4	RST1615S B1 ZW4S L BR	C3	signalbraun /signal brown
46.051.4153.6	RST1615S B1 ZW4S A TB	C2	türkisblau /turquoise blue
46.051.4153.1	RST1615S B1 ZW4 SW	C1	schwarz /black
46.051.4153.0	RST1615S B1 ZW4 GL	C1	lichtgrau /light grey
Bestellnummer /Order number	Typ /Type	Kodierung /Coding	Farbe /Colour

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

Toleranzierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung:
First Use: -

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff/Material

Maßstab/Scale 1:1

Vol. mm³ Oft./Surf. mm²

	Tag/Date	Name
2014		
gezeichnet drawn	13.02.	Winkler
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No. T 46.051.4153.0 13K

Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index | Datum / Blatt Date / Sheet
Änderung/Revision

wieland
www.wieland-electric.com

Type RST16..

Benennung/Title
BUCHSENTEIL
mit Zugentlastung, 5 polig
female connector with strain relief, 5 poles

QU-MEE-01/14 -

4605141530136_2 CADW3028 Tresc'on 2014-04-01T07:52:40 1.000