

product data sheet

item no. 92.934.0753.0

connector GST18I3F S2 ZR1 GN07

gesis® CLASSIC connector, number of poles 3, male, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 7.8 - 10.3 mm, color of coding/ contact carrier may green



item no.	92.934.0753.0
EAN	4049088260339
order unit	50 piece(s)

certificates / approvals



technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	2
mechanical coding	code 7
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	may green
Pole codification	1, PE, 2/N
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	6017

connection data

cable diameter max.	10.3 mm
cable diameter min.	7.8 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.5 mm²
connection cross section fine stranded mm² max.	1.5 mm²
connection cross section fine stranded mm² min.	0.5 mm²
terminations per pole	2
sheath strip length	45 mm
wire strip length	9 mm

model

model	male
connection type	spring clamp connection
degree of protection (IP)	IP40
remark to type of connection	fine stranded and stranded conductors require cable end sleeve

material

housing material	polyamide
------------------	-----------

halogen free	yes
contact material	CuZn
fire load	0.122 kWh/St
insulation components continuous temperature	100 °C
surface finish	tin-plated

dimensions

length	75 mm
width	32.5 mm
height	15.5 mm

accessories

item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
06.561.7853.0	mounting frame GST18i3 SW	Mounting frame to snap in GST18i3 connectors into a housing or furniture. Wall thickness: 1,5-2,5 mm. Holds GST18i3 connectors with screw or spring connection and pre- assembled cables.
05.561.3653.0	cover cap GST18i3VS B WS	Cover piece for female GST18i3, white
05.561.3653.1	cover cap GST18i3VS B SW	Cover piece for female GST18i3, black
05.564.5353.0	cover cap GST18i3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18i3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.594.4250.0	cover cap ST18/3B + GST18i3 ST WS	
05.594.4253.0	cover cap ST18/3B + GST18i3 ST WS	

assembly

item no.	type	description
92.033.0058.0	device connector GST18i3L B1H WS	gis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier white, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification L, N, PE, mechanical coding code 1, housing material polyamide, halogen free yes, fire load 0.029 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.033.0158.0	device connector GST18i3L B1H GR01	gis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier pebble grey, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification L, N, PE, mechanical coding code 2, housing material polyamide, halogen free yes, fire load 0.028 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.033.0658.0	device connector GST18i3L B1H BR05	gis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier brown, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification L, N, PE, mechanical coding code 4, housing material polyamide, halogen free yes, fire load 0.029 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.297.1003.0	cable assembly GST18i3KSB- 15 10TR01	gis® CLASSIC connection cable, female - free end, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier tomato red
92.033.0758.0	device connector GST18i3L B1H RT03	gis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier salmon pink, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification L, N, PE, mechanical coding code 3, housing material polyamide, halogen free yes, fire load 0.029 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.033.0858.0	device connector GST18i3L B1H H RT03	gis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier salmon pink, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification L, N, PE, mechanical coding code 3, housing material polyamide, halogen free yes, fire load 0.032 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.933.0753.0	connector GST18i3F B2 ZR1 GN07	gis® CLASSIC connector, number of poles 3, female, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 7.8 - 10.3 mm, color of coding/ contact carrier may green
92.033.0358.0	device connector GST18i3L B1H GN07	gis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier may green, degree of protection (ip) IP20,

		built-in component soldering connection, angle of plug square, pole codification 1, PE, 2/N, mechanical coding code 7, housing material polyamide, halogen free yes, fire load 0.029 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.033.0558.0	device connector GST18I3L B1H TB06	geis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification 1, 2, 3, mechanical coding code 6, housing material polyamide, halogen free yes, fire load 0.029 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm
92.297.1000.7	cable assembly GST18I3KSBS 15 10GN07	geis® CLASSIC connecting cable, female - male, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier may green
92.297.1004.7	cable assembly GST18I3KS-S 15 10GN07	geis® CLASSIC connection cable, male - free end, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier may green
92.033.0458.0	device connector GST18I3L B1H PB04	geis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier pastel blue, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification 1, 2, 3, mechanical coding code 5, housing material polyamide, halogen free yes, fire load 0.031 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 28.2 mm

